



30073J Wire-Nut Wire Conn, Model 73B Orange, 300/Jar *Ideal*

| | |
|------------------|---|
| Catalog Number | 30073J |
| Manufacturer | Ideal |
| Description | Twist-On Wire Nut, Orange Insulation Color, 1 to 5 Conductors, 600 V Ac |
| Weight per unit | N/A |
| Product Category | Electrical Fixture Conn (Nuts |

Features

| | |
|----------------|-------------------------------|
| Material | Flame-retardant Polypropelene |
| media | Yes |
| Voltage Rating | 600 |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Orange |
|-------|--------|

Descriptions

| | |
|------------------------|--|
| Description | WIRE-NUT WIRE CONN, MODEL 73B ORANGE, 300/JAR |
| extra long description | IDEAL 30-073J WIRENUT 73B ORANGE, 3 |
| Features | The IDEAL Wire-Nut Wire Connector set new standards for innovation, quality and convenience when it was first introduced in 1928. As the first screw-on wire connector in America, it literally set the industry standard for years to come. With a fixed, square-wire spring and a positive grip shell, the Wire-Nut is perfect to twist-on with fingers for a secure connection that will last. The refined wire range makes it the best choice for fine stranded wire applications. The Wire-Nut also features a tough, flame |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Ideal |
| GTIN | 00783250216789 |
| UPC | 783250216789 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------|
| Category Description | WIRE NUTS |
| Type | Twist-On |

Availability

| | |
|-------------|-----|
| minimum qty | 300 |
|-------------|-----|

Packaging

| | |
|-----------------|------|
| Carton | 300 |
| Package | 1800 |
| Weight Per each | 0 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Insulating or Joining 2 or more conductors |
| environmental conditions | Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F) |
| standard | CSA Certified to C22.2 #188, UL Listed to 486C, complies with Federal Specification W-S-610E |