

Eaton 3BR1836L200R

Catalog Number: 3BR1836L200R

Eaton BR main lug loadcenter, No feed-thru lugs, Main lug, 200 A, C3R, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 36 Circuits, 18 Spaces, Four-wire, Three-phase, Type BR 1-inch breakers, 208 Y/120, 240 V, #1 AWG-300 kcmil Cu/Al



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	3BR1836L200R
UPC	Product Length/Depth
786676442107	5.19 in
Product Height	Product Width
21 in	14.31 in
Product Weight	Warranty
28.7 lb	10 year
Certifications	Catalog Notes
UL 67 UL 50	Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard

Product specifications

Special features

No feed-thru lugs

Type

Main lug

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Number of circuits

36

Number of spaces

18

Phase

Three-phase

Used with

Type BR 1-inch breakers

Voltage rating

208Y/120, 240V

Wire size

#1 AWG-300 kcmil Cu/Al

Box size

C3R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

NEMA rating

NEMA 3R

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - 3BR1836L200R](#)

[3-Phase Loadcenter Program](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Number of wires

4



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton 3BR1836L200R

Catalog Number: 3BR1836L200R

Eaton BR main lug loadcenter, No feed-thru lugs, Main lug, 200 A, C3R, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 36 Circuits, 18 Spaces, Four-wire, Three-phase, Type BR 1-inch breakers, 208 Y/120, 240 V, #1 AWG-300 kcmil Cu/Al



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	3BR1836L200R
UPC	Product Length/Depth
786676442107	5.19 in
Product Height	Product Width
21 in	14.31 in
Product Weight	Warranty
28.7 lb	10 year
Certifications	Catalog Notes
UL 67 UL 50	Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard

Product specifications

Special features

No feed-thru lugs

Type

Main lug

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Number of circuits

36

Number of spaces

18

Phase

Three-phase

Used with

Type BR 1-inch breakers

Voltage rating

208Y/120, 240V

Wire size

#1 AWG-300 kcmil Cu/Al

Box size

C3R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

NEMA rating

NEMA 3R

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - 3BR1836L200R](#)

[3-Phase Loadcenter Program](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Number of wires

4



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)