



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 5851 SGL Recp 20A 250V S-Wire BR

*Pass & Seymour/Legrand*

Catalog Number	5851
Manufacturer	Pass & Seymour/Legrand
Description	Heavy-Duty Spec Grade Single Receptacle, Side Wire 20A 250V
Weight per unit	0.1604 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
Number of Wires	3
Outlet Type	Indoor, Commercial
Poles	2
Voltage	250.0 V
Voltage Rating	250
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

### Dimensions and Weight

Height	3.68
Width	1.08

### Descriptions

Description	SGL RECP 20A 250V S-WIRE BR
extra long description	P&S 5851 RECP SGL 20A 250V S-WIRE B
Long Description	Heavy-Duty Spec Grade Single Receptacle, Side Wire 20A 250V
Product Type	Recp SGL 20A 250V S-Wire BN
Special Features	Auto-ground clip assures positive ground. Two drive screws anchor strap to back body and face where abrupt removal torque is greatest. Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength. Backed-out tri-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility. One-piece brass triple-wire power contacts for lasting retention.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007585100
Manufacturers Part Number	5851
UPC	785007585100

## Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	10
Package	100
Weight Per each	0.1604

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	6-20R
standard	CULUS, UL498, CSA C22.2 No. 42