



SAFETY DATA SHEET

METACAULK® MC 150+

General purpose firestop sealant

SECTION 1 – PRODUCT AND COMPANY INFORMATION

Product Name

Metacaulk® MC 150+

Product Codes

66382, 66383, 66385, 66389, 66648

Chemical Family

Organic/Inorganic

Use

Firestopping sealant

Manufacturer's Name

The RectorSeal Corporation
2601 Spenwick Drive
Houston, Texas 77055 USA

Date of Validation

August 21, 2017

Date of Preparation

August 21, 2017

HMIS Codes

Health	1
Flammability	0
Reactivity	0
PPI	B

Emergency Telephone No.

Chemtrec 24 Hours
(800)-424-9300 USA
(703)-527-3887 International

Technical Service Telephone No.

(800)-231-3345 or (713)-263-8001

SECTION 2 – HAZARDS IDENTIFICATION

GHS CLASSIFICATION

Physical Hazards:

None

Health Hazards

Acute Toxicity:

Oral: Not Classified

Dermal: Not Classified

Inhalation: Not Classified

Skin Corrosion/Irritation: Not Classified

Serious Eye Damage/Eye Irritation: Not Classified

Respiratory or Skin Sensitization: Not Classified

Germ Cell Mutagenicity: Not Classified

Carcinogenicity: Not Classified

Reproductive Toxicology: Not Classified

Target Organ Systemic Toxicity - Single Exposure: Not Classified

Target Organ Systemic Toxicity - Repeated Exposure: Not Classified

Aspiration Toxicity: Not Classified

ENVIRONMENTAL HAZARDS

Hazardous to the Aquatic Environment: Not Classified
Acute aquatic toxicity: Not Classified
Chronic aquatic toxicity: Not Classified
Bioaccumulation potential: Not Classified
Rapid degradability: Not Classified

GHS Label elements, including precautionary statements

Pictogram: None

Signal Word: None

Hazard Statements:
None

Precautionary Statements:
P102 - Keep out of reach of children.
P264 - Wash hands thoroughly after handling.

Classification according to EU Directives 67/548/EEC or 1999/45/EC

Labeling Symbols: None

Risk R-Phrases: None

Safety S-Phrases:
S2: Keep out of the reach of children.

Summary Of Acute Hazards

May cause skin irritation.

Route Of Exposure, Signs And Symptoms

INHALATION

Not a respiratory irritant.

EYE CONTACT

Contact may cause eye irritation.

SKIN CONTACT

Contact may cause skin irritation.

INGESTION

Possible irritation to mucous membranes of the mouth, throat, and stomach.

SUMMARY OF CHRONIC HAZARDS

None known.

MEDICAL CONDITIONS AGGRAVATED BY EXPOSURE

Persons with pre-existing skin conditions or chemical allergies may be more susceptible to contact effects of the cured elastomer.

SECTION 3 – COMPOSITION/INFORMATION ON INGREDIENTS

% by WT

CAS No. INGREDIENT UNITS

None as defined by OSHA Hazard Communication Standard 29 CFR 1910.1200.

SECTION 4 – FIRST AID MEASURES

- If inhaled: Not a respiratory irritant.
- If on skin: Wash with soap and water. If irritation occurs, seek medical attention.
- If in eyes: Immediately flush with large amounts of water. If irritation occurs, seek medical attention.
- If swallowed: If swallowed, call a physician immediately. Only induce vomiting at the instruction of a physician. Never give anything by mouth to an unconscious person.

SECTION 5 – FIRE FIGHTING MEASURES

Extinguishing Media

Foam, dry chemical, carbon dioxide or water fog.

Special Fire Fighting Procedures: Wear self-contained breathing apparatus (SCBA) and other protective clothing. Hazardous decomposition products possible (see Section 10).

Unusual Fire And Explosion Hazards: Heat may build up and rupture closed containers.

SECTION 6 – ACCIDENTAL RELEASE MEASURES

Steps To Be Taken In Case Material Is Released Or Spilled: Wipe up spills to prevent footing hazard. Avoid flushing into sewers, drains, waterways and soil. Wear protective clothing during clean up.

SECTION 7 – HANDLING AND STORAGE

Precautions To Be Taken In Handling And Storing: Keep container closed and upright when not in use. To prevent freezing and possible rupture of container, do not store below 35°F.

Other Precautions: Avoid prolonged or repeated contact with skin or clothing. Empty containers may contain residues and vapors; treat as if full and observe all product precautions. Do not reuse empty containers.

KEEP OUT OF REACH OF CHILDREN.

SECTION 8 – EXPOSURE CONTROLS/PERSONAL PROTECTION

Respiratory Protection (Specify Type): None required.

Ventilation – Local Exhaust: N/A

Special: N/A

Mechanical (General): N/A

Other: N/A

Protective Gloves: None required.

Eye Protection: None required.

Other Protective Clothing Or Equipment: None required.

Work/Hygienic Practices: Where use can result in skin contact, wash exposed areas thoroughly before eating, drinking, smoking, or leaving work area. Launder contaminated clothing before reuse.

SECTION 9 – PHYSICAL AND CHEMICAL PROPERTIES

Boiling point:	212°F (100°C) @ 760mm Hg
Specific gravity (H2O = 1):	1.5
Vapor pressure (mmHg):	17 @ 68°F (20°C)
Melting point:	N/A
Vapor Density (Air = 1):	N/A
Evaporation rate (Ethyl Acetate = 1):	> 1
Appearance/Odor:	Red paste/Mild odor
Solubility in water:	Soluble
Volatile Organic Compounds (VOC) Content (theoretical percentage by weight):	< 1% or (< 10 g/L)
Flash point:	None
Lower explosion limit:	None
Upper explosion limit:	None

SECTION 10 – STABILITY AND REACTIVITY

Stability: Stable

Conditions To Avoid: None.

Incompatibility (Materials To Avoid): None known.

Hazardous Decomposition Products: CO, CO₂ and fragmented hydrocarbons.

Hazardous Polymerization: Will not occur.

SECTION 11 – TOXICOLOGY INFORMATION

Chronic Health Hazards

No ingredient in this product is an IARC, NTP or OSHA Lister carcinogen.

Toxicology Data

Ingredient Name

None

SECTION 12 – ECOLOGICAL INFORMATION

Ecological Data

Ingredient Name:	None
Food Chain Concentration Potential:	N/A
Waterfowl Toxicity:	N/A
BOD:	N/A
Aquatic Toxicity:	N/A

SECTION 13 – DISPOSAL CONSIDERATIONS

Waste Classification: Non-regulated solid waste

Disposal Method: Approved landfill

Waste from this product is not considered hazardous as defined under the Resource Conservation and Recovery Act (RCRA) 40 CFR 261. Dispose of in accordance with federal, state, and local regulation regarding pollution.

SECTION 14 – TRANSPORTATION INFORMATION

DOT:	Non-regulated
Ocean (IMDG):	Non-regulated
Air (IATA):	Non-regulated
WHMIS (Canada):	Non-regulated

SECTION 15 – REGULATORY INFORMATION

Regulatory Data

Ingredient Name:	None
SARA 313	N/A
TSCA Inventory	All components listed
CERCLA RQ	N/A
RCRA Code	N/A

SECTION 16 – OTHER INFORMATION

This document is prepared pursuant to the OSHA Hazard Communication Standard (29 CFR 1910.1200). The information herein is given in good faith, but no warranty, expressed or implied is made.

Consult RectorSeal for further information: (713) 263-8001



SAFETY DATA SHEET

METACALK® MC 150+

General purpose firestop sealant

SECTION 1 – PRODUCT AND COMPANY INFORMATION

Product Name

Metacalk® MC 150+

Product Codes

66382, 66383, 66385, 66389, 66648

Chemical Family

Organic/Inorganic

Use

Firestopping sealant

Manufacturer's Name

The RectorSeal Corporation
2601 Spenwick Drive
Houston, Texas 77055 USA

Date of Validation

August 21, 2017

Date of Preparation

August 21, 2017

HMIS Codes

Health	1
Flammability	0
Reactivity	0
PPI	B

Emergency Telephone No.

Chemtrec 24 Hours
(800)-424-9300 USA
(703)-527-3887 International

Technical Service Telephone No.

(800)-231-3345 or (713)-263-8001

SECTION 2 – HAZARDS IDENTIFICATION

GHS CLASSIFICATION

Physical Hazards:

None

Health Hazards

Acute Toxicity:

Oral: Not Classified

Dermal: Not Classified

Inhalation: Not Classified

Skin Corrosion/Irritation: Not Classified

Serious Eye Damage/Eye Irritation: Not Classified

Respiratory or Skin Sensitization: Not Classified

Germ Cell Mutagenicity: Not Classified

Carcinogenicity: Not Classified

Reproductive Toxicology: Not Classified

Target Organ Systemic Toxicity - Single Exposure: Not Classified

Target Organ Systemic Toxicity - Repeated Exposure: Not Classified

Aspiration Toxicity: Not Classified

ENVIRONMENTAL HAZARDS

Hazardous to the Aquatic Environment: Not Classified
Acute aquatic toxicity: Not Classified
Chronic aquatic toxicity: Not Classified
Bioaccumulation potential: Not Classified
Rapid degradability: Not Classified

GHS Label elements, including precautionary statements

Pictogram: None

Signal Word: None

Hazard Statements:
None

Precautionary Statements:
P102 - Keep out of reach of children.
P264 - Wash hands thoroughly after handling.

Classification according to EU Directives 67/548/EEC or 1999/45/EC

Labeling Symbols: None

Risk R-Phrases: None

Safety S-Phrases:
S2: Keep out of the reach of children.

Summary Of Acute Hazards

May cause skin irritation.

Route Of Exposure, Signs And Symptoms

INHALATION

Not a respiratory irritant.

EYE CONTACT

Contact may cause eye irritation.

SKIN CONTACT

Contact may cause skin irritation.

INGESTION

Possible irritation to mucous membranes of the mouth, throat, and stomach.

SUMMARY OF CHRONIC HAZARDS

None known.

MEDICAL CONDITIONS AGGRAVATED BY EXPOSURE

Persons with pre-existing skin conditions or chemical allergies may be more susceptible to contact effects of the cured elastomer.

SECTION 3 – COMPOSITION/INFORMATION ON INGREDIENTS

% by WT

CAS No. INGREDIENT UNITS

None as defined by OSHA Hazard Communication Standard 29 CFR 1910.1200.

SECTION 4 – FIRST AID MEASURES

- If inhaled: Not a respiratory irritant.
- If on skin: Wash with soap and water. If irritation occurs, seek medical attention.
- If in eyes: Immediately flush with large amounts of water. If irritation occurs, seek medical attention.
- If swallowed: If swallowed, call a physician immediately. Only induce vomiting at the instruction of a physician. Never give anything by mouth to an unconscious person.

SECTION 5 – FIRE FIGHTING MEASURES

Extinguishing Media

Foam, dry chemical, carbon dioxide or water fog.

Special Fire Fighting Procedures: Wear self-contained breathing apparatus (SCBA) and other protective clothing. Hazardous decomposition products possible (see Section 10).

Unusual Fire And Explosion Hazards: Heat may build up and rupture closed containers.

SECTION 6 – ACCIDENTAL RELEASE MEASURES

Steps To Be Taken In Case Material Is Released Or Spilled: Wipe up spills to prevent footing hazard. Avoid flushing into sewers, drains, waterways and soil. Wear protective clothing during clean up.

SECTION 7 – HANDLING AND STORAGE

Precautions To Be Taken In Handling And Storing: Keep container closed and upright when not in use. To prevent freezing and possible rupture of container, do not store below 35°F.

Other Precautions: Avoid prolonged or repeated contact with skin or clothing. Empty containers may contain residues and vapors; treat as if full and observe all product precautions. Do not reuse empty containers.

KEEP OUT OF REACH OF CHILDREN.

SECTION 8 – EXPOSURE CONTROLS/PERSONAL PROTECTION

Respiratory Protection (Specify Type): None required.

Ventilation – Local Exhaust: N/A

Special: N/A

Mechanical (General): N/A

Other: N/A

Protective Gloves: None required.

Eye Protection: None required.

Other Protective Clothing Or Equipment: None required.

Work/Hygienic Practices: Where use can result in skin contact, wash exposed areas thoroughly before eating, drinking, smoking, or leaving work area. Launder contaminated clothing before reuse.

SECTION 9 – PHYSICAL AND CHEMICAL PROPERTIES

Boiling point:	212°F (100°C) @ 760mm Hg
Specific gravity (H2O = 1):	1.5
Vapor pressure (mmHg):	17 @ 68°F (20°C)
Melting point:	N/A
Vapor Density (Air = 1):	N/A
Evaporation rate (Ethyl Acetate = 1):	> 1
Appearance/Odor:	Red paste/Mild odor
Solubility in water:	Soluble
Volatile Organic Compounds (VOC) Content (theoretical percentage by weight):	< 1% or (< 10 g/L)
Flash point:	None
Lower explosion limit:	None
Upper explosion limit:	None

SECTION 10 – STABILITY AND REACTIVITY

Stability: Stable

Conditions To Avoid: None.

Incompatibility (Materials To Avoid): None known.

Hazardous Decomposition Products: CO, CO₂ and fragmented hydrocarbons.

Hazardous Polymerization: Will not occur.

SECTION 11 – TOXICOLOGY INFORMATION

Chronic Health Hazards

No ingredient in this product is an IARC, NTP or OSHA Lister carcinogen.

Toxicology Data

Ingredient Name

None

SECTION 12 – ECOLOGICAL INFORMATION

Ecological Data

Ingredient Name:	None
Food Chain Concentration Potential:	N/A
Waterfowl Toxicity:	N/A
BOD:	N/A
Aquatic Toxicity:	N/A

SECTION 13 – DISPOSAL CONSIDERATIONS

Waste Classification: Non-regulated solid waste

Disposal Method: Approved landfill

Waste from this product is not considered hazardous as defined under the Resource Conservation and Recovery Act (RCRA) 40 CFR 261. Dispose of in accordance with federal, state, and local regulation regarding pollution.

SECTION 14 – TRANSPORTATION INFORMATION

DOT:	Non-regulated
Ocean (IMDG):	Non-regulated
Air (IATA):	Non-regulated
WHMIS (Canada):	Non-regulated

SECTION 15 – REGULATORY INFORMATION

Regulatory Data

Ingredient Name:	None
SARA 313	N/A
TSCA Inventory	All components listed
CERCLA RQ	N/A
RCRA Code	N/A

SECTION 16 – OTHER INFORMATION

This document is prepared pursuant to the OSHA Hazard Communication Standard (29 CFR 1910.1200). The information herein is given in good faith, but no warranty, expressed or implied is made.

Consult RectorSeal for further information: (713) 263-8001