

24V Dimmable 60W Power Supply BKT

6TD24V60BKT (Textured Black)

Project Name: _____

Location: _____

Type: _____

Qty: _____

Comments: _____



Ordering Information

| | |
|------------|----------------|
| Product ID | 6TD24V60BKT |
| Finish | Textured Black |

Specifications

| | |
|----------|-------|
| Material | Metal |
|----------|-------|

Electrical

| | |
|---------------|-------------|
| Dimmable | Yes |
| Voltage | 108-132V |
| Input Voltage | Single(120) |

Qualifications

| | |
|--------------------|--|
| Safety Rated | Damp |
| Class 2 | Yes |
| Expected Life Span | 50000 Hours |
| Warranty | www.kichler.com/warranty |

Installation

| | |
|---------------------|-----------|
| Wire Connectors | Wire Nuts |
| Direct Wire | Yes |
| Knockouts | 1 in |
| Number of Knockouts | 4 |

Dimensions

| | |
|--------|-------|
| Height | 1.25" |
| Length | 4.50" |
| Width | 7.25" |

Notes:

1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.

2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.

24V Dimmable 60W Power Supply BKT

6TD24V60BKT (Textured Black)

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____



Ordering Information

| | |
|------------|----------------|
| Product ID | 6TD24V60BKT |
| Finish | Textured Black |

Specifications

| | |
|----------|-------|
| Material | Metal |
|----------|-------|

Electrical

| | |
|---------------|-------------|
| Dimmable | Yes |
| Voltage | 108-132V |
| Input Voltage | Single(120) |

Qualifications

| | |
|--------------------|--|
| Safety Rated | Damp |
| Class 2 | Yes |
| Expected Life Span | 50000 Hours |
| Warranty | www.kichler.com/warranty |

Installation

| | |
|---------------------|-----------|
| Wire Connectors | Wire Nuts |
| Direct Wire | Yes |
| Knockouts | 1 in |
| Number of Knockouts | 4 |

Dimensions

| | |
|--------|-------|
| Height | 1.25" |
| Length | 4.50" |
| Width | 7.25" |

Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.