



71A6452001D 750W MH Bal

Advance By Signify

Catalog Number	71A6452001D
Manufacturer	Advance By Signify
Description	Reliable Performance Vacuum-Pressure Impregnation Is Used to Re-Enforce The Electrical Insulation Of The Ballast, Preclude Moisture, Inhibit Noise, and Dissipate Heat; Pre-Insulated Voltage Leads Reduce The Risk Of Shock and Shrink Installation Time The Basic Ballast Is The Open Core and Coil Which Is Most Often Used As A Component Within A Lighting Luminaire. The Core and Coil Also Forms The Nucleus Of Philips Advance'S Five Other Ballast Configurations. Vacuum-Pressure Impregnated With A Silica-Filled Pol
Weight per unit	20.2 (lbs/each)
Product Category	Hid Ballast Kits

Features

ANSI Code	M149
Ballast Factor	1
dimmable	No
Lamp Type	METAL HALIDE
Number of Lamps	1
Power Factor	0.90
Power Rating	750
start type	Pulse
Voltage Rating	120/208/240/277/480
Wattage	750

Dimensions and Weight

Height	16.73
Length	0.24
Width	1.69



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8420 Tejas Loop
78045-0000, TX Laredo
Phone: 956-462-0607
Fax: 956-284-6601

Descriptions

Description	750W MH BAL
extra long description	ADV 71A6452001D MH BAL 750W M149 5-
Long Description	Reliable performance Vacuum-pressure impregnation is used to re-enforce the electrical insulation of the ballast, preclude moisture, inhibit noise, and dissipate heat; Pre-insulated voltage leads reduce the risk of shock and shrink installation time. The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations. Vacuum-pressure impregnated with a silica-filled pol
Product Type	MH Bal 750W M149 5-Tap Kit

Manufacturer Information

Brand	Signify Electronics
GTIN	00781087057490
Manufacturers Part Number	71A6452001D
UPC	781087057490

Taxonomies, Classifications, and Categories

Category Description	HID BALLASTS
Type	Magnetic HID

Packaging

Carton	1
Weight	20.16
Weight Per each	20.16

Uses, Certifications, and Standards

Application	Lighting Luminaire Component
Frequency Rating	60
standard	ULR: CSA certificate: RoHS Compliant