



## 850G 2-1/2" & 3" CVR W/Intg Gasket

*Crouse-Hinds*

Catalog Number	850G
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Series 5 Integral Gasket Cover, Aluminum, 2-1/2" or 3"
Weight per unit	1.0 (lbs/each)
Product Category	Alum

### Features

connection	Threaded / Set Screw
dimensions	12.0000 IN X 0.7500 IN X 4.2500 IN
Form	Series 5

### Material, Color, and Finish

Color	Gray
Finish	Epoxy Powder Coat

### Dimensions and Weight

Hub Size	2-1/2 In, 3 In
----------	----------------

### Descriptions

Description	2-1/2" & 3" CVR W/INTG GASKET
extra long description	CRS-H 850G 2 1/2 & 3 SERIES 5 INTEG
Features	Eaton's Crouse-Hinds Division Series 5 die cast copper-free aluminum conduit bodies, covers and gaskets are available for use with rigid or EMT conduit (with set screw). Conduit bodies are available in trade sizes 1/2" to 4", in the most popular conduit body shapes (C, LB, LL, LR, T) and 1/2" to 2" in TB and X shapes. The Series 5 family is available as components or pre-packaged in various configurations as a SnapPack assembly. In addition, Series 5 is completely interchangeable with other manufacturer
Long Description	Eaton Crouse-Hinds series Condulet Series 5 integral gasket cover, Aluminum, 2-1/2" or 3"
Product Type	2 1/2 & 3 Series 5 Integral Gasket Cover
Special Features	Corrosion Resistant

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00662277005616
Manufacturers Part Number	850G
UPC	662277005616



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Integral gasket cover

## Packaging

Carton	1
Package	10
Weight Per each	1

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure	Condulet
Mounting	Conduit
standard	UL, cUL