

Night Com™ Combo LED/Incandescent Flashlight

Case Material: Corrosion and water resistant, Mil Spec Type II anodized machined aluminum for superior wear and abrasion resistance.

Dimensions: Length: 5.43 in (13.79 cm)

Diameter: Major Diameter: 1.33 in. (3.38 cm)

Body Diameter: 0.98 in. (2.49 cm)

Weight: 5.44 oz (152 grams)*

Lens: Unbreakable polycarbonate lens

Light Source: 4.8 Volt, 0.9A high pressure xenon bulb
100,000 hour life LEDs; 2 Ultra-Bright and 1 Indicator type

Light Output: LED Rating (Ultra-Bright): 8 Lumens typical (2 Red LEDs)
Bulb Rating: 72 Lumens Typical (Xenon)
Indicator Type Red LED: Preserves complete dark adaptation per MIL-1472D

On/Off: Mode Select Sequence: (2) Ultra-Bright LEDs / (1) Indicator-type LED / Xenon / Safe
Tailcap switch: On/Off and Signal

Run Time: Up to 2.5 hours (Xenon Bulb); Up to 28 hours (LEDs)

Battery: Two (2) 3V CR123A lithiumbatteries

- Features:
- Dual Switch System features an engineered tailcap switch for Power On/Off and Signal
 - Glow-in-the-dark marker on the mode switch
 - 2 Ultra-Bright Red LEDs, 1 low power LED for optimum night vision protection
 - O-Ring sealed
 - Water resistant
 - Heavy duty drop tested construction
 - Knurled grip
 - Wrist lanyard

Approvals: Most models meet applicable European Community Directives.

Warranty: Limited lifetime warranty.



* With batteries (Included in purchase)
Made in China



Item	UPC	Part #
Night Com Red LEDs	080926-51021-0	51021
Lithium batteries (2) Pack	080926-85175-7	85175
Lithium batteries (12) Pack	080926-85177-1	85177
Lithium batteries (400) Pack	080926-85179-5	85179

