



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

430 South Fletcher  
75951-0000, TX Jasper  
Phone: 409-489-0056  
Fax: 409-489-0059



## A515MW 15 Min Twist Timer White

*Nsi Industries*

Catalog Number	A515MW
Manufacturer	Nsi Industries
Description	Interval Timer 15 Min White
Weight per unit	0.4000 (lbs/each)
Product Category	Electromechanical Time Switches

### Features

action	SPDT
Base	Wall Plate
Contact Rating	125-250-277 VAC
Phase	Single Phase
Poles	1
Timing Range	15 Minute

### Dimensions and Weight

Size	H=5.00 - W=3.00
------	-----------------

### Descriptions

Description	15 MIN TWIST TIMER WHITE
extra long description	TORK A515MW 15 Minute Spring Wound
Features	Tork 15 min Twist Timer No Hold- White APPLICATIONS: Whole House Fans, Indoor/Outdoor Lighting, Bathroom Fans and Lights, Self Storage. FEATURES: COLOR: White VARIABLE TIMING: Twist knob for time ON setting up to 15 minutes. HOLD FEATURE: No Hold on this model. EASY SET : No adjustments. Just wire and go, EASY WIRING: No neutral required. Great for retrofit, Use as single or in multi-gang box with no de-rating. SWITCH TYPE: SPST "2 in 1" contacts wire has SPST also WALL PLATE: Fits standard or decorator st
Long Description	Interval Timer 15 Min White
Product Type	15 Minute Spring Wound Twist Timer 125-277V SPDT White
Special Features	White 15 Minute No Hold In Wall Time Switch

### Manufacturer Information

Brand	TORK
GTIN	00786261151131
Manufacturers Part Number	A515MW
UPC	786261151131

### Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	Spring Wound In Wall Time Switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

430 South Fletcher  
75951-0000, TX Jasper  
Phone: 409-489-0056  
Fax: 409-489-0059

## Packaging

Carton	1
Weight Per each	0.4

## Uses, Certifications, and Standards

Application	NSI
Enclosure	Single Gang Wall Plate
environmental conditions	32-122 F
Frequency Rating	50-60 Hz
Mounting	Single Gang Wall Plate
Operating Temperature	32-122 F
standard	cULus