



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



8630 2", 30D Emt Elb *Topaz - Southwire LLC*

Catalog Number	8630
Manufacturer	Topaz - Southwire LLC
Description	Emt Conduit Elbow, Steel Material; Galvanized Finish; UI (Canada and Us), UI 797, Csa Approval; Ansi C80.3, Federal Specification WW-C-563 Applicable Standard; 10 Per Case Standard Package; 2 Inch Trade Size; Plain End Type; 30 Degree Bend Angle
Weight per unit	1.9 (lbs/each)
Product Category	Emt to Emt Pulling Elbows

Features

Applicable Standard	ANSI C80.3, Federal Specification WW-C-563
Bend Angle	30 Degree
Bend Radius	9.5 INCH
End Type	Plain
Material	Steel

Material, Color, and Finish

Finish	Galvanized
--------	------------

Descriptions

Commodity Description	Emt To Emt Pulling Elbows
Description	2",30D EMT ELB
extra long description	STEEL MATERIAL; GALVANIZED FINISH; UL (CANADA AND US), UL 797, CSA APPROVAL; ANSI C80.3, FEDERAL SPECIFICATION WW-C-563 APPLICABLE STANDARD; 10 PER CASE STANDARD PACKAGE; 2 INCH TRADE SIZE; PLAIN END TYPE; 30 DEGREE BEND ANGLE; 9.5 INCH BEND RADIUS
Long Description	EMT CONDUIT ELBOW, STEEL MATERIAL; GALVANIZED FINISH; UL (CANADA AND US), UL 797, CSA APPROVAL; ANSI C80.3, FEDERAL SPECIFICATION WW-C-563 APPLICABLE STANDARD; 10 PER CASE STANDARD PACKAGE; 2 INCH TRADE SIZE; PLAIN END TYPE; 30 DEGREE BEND ANGLE
Product Type	Emt Conduit Elbow

Manufacturer Information

Brand	Southwire Rough Electrical Com
GTIN	00751338839052
Manufacturers Part Number	8630
UPC	751338839052

Taxonomies, Classifications, and Categories

Category Description	EMT ELBOWS
----------------------	------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Trade Size 2 INCH

Packaging

Carton 1

Standard Package 10 PER CASE

Weight Per each 1.895

Uses, Certifications, and Standards

Approval UL (Canada and US), UL 797, CSA