



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1501 Heritage Parkway Suite 101
76063-0000, TX Mansfield
Phone: 682-518-7272
Fax: 682-518-7255



A20H1608GQRLP Hoff A20H1608GQRLP NM4X FBRGLS Enc

Hoffman Enclosures, Inc.

Catalog Number	A20H1608GQRLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Hinge Cover Enclosure Quick-Release Type 4X, 20.19X16.25X8.00, Gray, Fiberglass
Weight per unit	19.8 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

Features

ip rating	IP66
-----------	------

Material, Color, and Finish

Color	Gray
Finish	Smooth Matte

Dimensions and Weight

Depth	8
Height	20.19
Size	20.19x16.25x8.00 in
Width	16.25

Descriptions

Description	HOFF A20H1608GQRLP NM4X FBRGLS ENC
extra long description	NVENT HOF A20H1608GQRLP Enclosure 2
Features	A full range of modification options are available for wall-mount fiberglass enclosures, including variable depths to accommodate larger controls. These enclosures feature padlockable polyester latches, or HOFFMAN's exclusive PowerGlide Handle with 3-point latching, for ease of access with increased security.
Long Description	Hinge Cover Enclosure Quick-Release Type 4X, 20.19x16.25x8.00, Gray, Fiberglass
Product Type	Enclosure 20.19X16.25X8.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510295004
Manufacturers Part Number	A20H1608GQRLP
UPC	783510295004

Taxonomies, Classifications, and Categories

Category Description	VYNCKER FIBERGLASS ENCLOSURES
Type	Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1501 Heritage Parkway Suite 101
76063-0000, TX Mansfield
Phone: 682-518-7272
Fax: 682-518-7255

Packaging

Carton	1
Weight Per each	19.8

Uses, Certifications, and Standards

Application	Controls and Drives;Corrosive Environments
nema rating	4X