



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ADR6044 60A 4W4P P&S Recpt (600VAC/250VDC)

Appleton/Oz Gedney



| | |
|------------------|---|
| Catalog Number | ADR6044 |
| Manufacturer | Appleton/Oz Gedney |
| Description | Pin and Sleeve Receptacle, 60 A, 600 V Ac 3 Phase @ 50 to 400 HZ 250 V DC, 4 Poles, 4 Wires, Epoxy Powder Coated Copper Free Aluminum, 1-1/4 In;1-1/2 In Hub Size, -40 °C Operating Temperature, +107 °C Operating Temperature, Pressure Wire Terminal, #6 to #2 Awg (Building);#6 to #4 Awg (Extra Flex) Wire Size, 3 LB |
| Weight per unit | 3.0 (lbs/each) |
| Product Category | Pin & Sleeve Devices |

Features

| | |
|-----------------|------------------------|
| amperage rating | 60 |
| connection | Pressure Wire Terminal |
| Number of Wires | 4 |
| Phase | 3 |
| Poles | 4 |

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | 60A 4W4P P&S RECPT (600VAC/250VDC) |
| extra long description | APP ADR6044 60A RECPT 4PS1 SCR/SPRG |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Appleton |
| GTIN | 00781381186438 |
| UPC | 781381186438 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------|
| Category Description | Pin & Sleeve Devices |
| Type | Grounding Style 1 Receptacle |

Packaging

| | |
|-----------------|---|
| Carton | 2 |
| Package | 6 |
| Weight Per each | 3 |

Uses, Certifications, and Standards

| | |
|-------------------|---|
| Application | For ACP6044BC Metallic Clamping Ring Plug |
| Mounting standard | BOX CSA Certified: 065179;CSA Standard: C22.2 No. 182.1;NEMA FB11;UL 1682, UL 1686, UL 50E;UL Listed: E145916, E145917 |