




AH8200



AH8200\_M




8310



IG8362

## Hospital Specification Grade Straight Blade Receptacles

2-Pole, 3-Wire Grounding  
15A, 125V/AC  
20A, 125V/AC  
NEMA 5-15R, 5-20R



### Premium Hospital Grade Receptacles

Back Wire & Side Wire	15A, 125V NEMA 5-15R	UL FUL S SP NOM 426	20A, 125V NEMA 5-20R	UL FUL S SP NOM 426
Description	Catalog No. Color Suffix		Catalog No. Color Suffix	
Premium Duplex Receptacle	<input type="checkbox"/> AH8200 B, BK, GY, RD, V, W	•	<input type="checkbox"/> AH8300 B, BK, GY, LA, RD, V, W	•
Premium Illuminated Duplex Receptacle	<input type="checkbox"/> AH8200LT RD, V, W	•	<input type="checkbox"/> AH8300LT RD, V, W	•
Premium Single Receptacle	<input type="checkbox"/> 8210 B, GY, RD, V, W	•	<input type="checkbox"/> 8310 B, GY, RD, V, W	•

### Premium Decorator Hospital Grade Receptacles

Back Wire & Side Wire	15A, 125V NEMA 5-15R	UL FUL S SP NOM 426	20A, 125V NEMA 5-20R	UL FUL S SP NOM 426
Description	Catalog No. Color Suffix		Catalog No. Color Suffix	
Premium Decorator Duplex Receptacle	<input type="checkbox"/> 8262 B, BK, GY, RD, V, W	•	<input type="checkbox"/> 8362 B, BK, GY, RD, V, W	•
Premium Decorator Illuminated Duplex Receptacle	<input type="checkbox"/> 8262LT GY, RD, V, W	•	<input type="checkbox"/> 8362LT RD, V, W	•

### Isolated Ground Premium Hospital Grade Receptacles

Back Wire & Side Wire	15A, 125V NEMA 5-15R	UL FUL S SP NOM 426	20A, 125V NEMA 5-20R	UL FUL S SP NOM 426
Description	Catalog No. Color Suffix		Catalog No. Color Suffix	
Premium IG Duplex Receptacle	<input type="checkbox"/> IG8200 GY, RD, RN, V, W	•	<input type="checkbox"/> IG8300 GY, RD, RN, V, W	•
Premium IG Single Receptacle	<input type="checkbox"/> IG8210 RN	•	<input type="checkbox"/> IG8310 RN	•
Premium IG Decorator Duplex Receptacle	<input type="checkbox"/> IG8262 GY, RN, V, W	•	<input type="checkbox"/> IG8362 GY, RN, V, W	•

\* Not Fed. Spec.

### Color Ordering Information

For ordering receptacles, include Cat. No. followed by the color code: A (Almond), B (Brown), BK (Black), BL (Blue), GY (Gray), LA (Light Almond), RD (Red), RN (Orange), V (Ivory), W (White)

### Icon Key

➡ ArrowLink™ option available. Add "M" suffix to Standard catalog number (example AH8300W, AH8300WM). For ordering information on ArrowLink & ArrowLink SPD connectors, see page A-3.

● Hospital Grade

🏠 Build-To-Spec Customizable Devices - see page A-4  
🇺🇸 NAFTA Compliant - see page O-30

### Specification Information:

Premium HG Receptacles: A-24

ArrowLink Premium HG Receptacles: A-28 & A-29

Isolated Ground Premium HG Receptacles: A-25

## Hospital Specification Grade Premium Receptacles

2-Pole, 3-Wire Grounding  
15A, 125V/AC; 15A, 250V/AC; 20A, 125V/AC; 20A 250V/AC  
NEMA 5-15, 6-15, 5-20, 6-20

	Device Type	Hospital Grade Premium Duplex Receptacles: AH8200, AH8300, AH8400, AH8600 Series	Hospital Grade Premium Decorator Duplex Receptacles: 8262, 8362 Series	Hospital Grade Premium Single Receptacles: 8210, 8310, 8410, 8610 Series
	Wiring Type	Back & side wire	Back & side wire	Back & side wire
	Testing & Code Compliance	<ul style="list-style-type: none"> <li>Listed to UL 498, file no. E15058</li> </ul>	<ul style="list-style-type: none"> <li>Listed to UL 498, file no. E15058</li> </ul>	<ul style="list-style-type: none"> <li>Listed to UL 498, file no. E15058</li> </ul>
		<ul style="list-style-type: none"> <li>UL verified to Federal Spec. WC-596G</li> </ul>	<ul style="list-style-type: none"> <li>UL verified to Federal Spec. WC-596G</li> </ul>	<ul style="list-style-type: none"> <li>UL verified to Federal Spec. WC-596G</li> </ul>
		<ul style="list-style-type: none"> <li>CSA certified to C22.2, no. 42, file no. 6914 (6233-01)</li> </ul>	<ul style="list-style-type: none"> <li>CSA certified to C22.2, no. 42, file no. 6914 (6233-01)</li> </ul>	<ul style="list-style-type: none"> <li>CSA certified to C22.2, no. 42, file no. 6914 (6233-01)</li> </ul>
		<ul style="list-style-type: none"> <li>NOM certified</li> </ul>	<ul style="list-style-type: none"> <li>NOM certified</li> </ul>	<ul style="list-style-type: none"> <li>NOM certified</li> </ul>
Specifications: Environmental	Flammability	Meets UL 94 requirements; V2 rated	Meets UL 94 requirements; V2 rated	Meets UL 94 requirements; V2 rated
	Temperature Rating	-20°C to 90°C (-4°F to 194°F)	-20°C to 70°C (-4°F to 158°F)	-20°C to 90°C (-4°F to 194°F)
Specifications: Electrical	Dielectric Voltage	Withstands 2000V per UL 498	Withstands 2000V per UL 498	Withstands 2000V per UL 498
	Current Interrupting	Yes, at full-rated current	Yes, at full-rated current	Yes, at full-rated current
	Temperature Rise	Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)
Specifications: Mechanical	Terminal Accommodation	#14 - 10 AWG	#14 - 10 AWG	#14 - 10 AWG
	Voltage Ratings	Permanently marked on device	Permanently marked on device	Permanently marked on device
Materials:	Face	Nylon	Nylon	Nylon
	Base	Glass-filled nylon	Glass-filled nylon	Nylon
	Strap	0.05" thick brass, nickel plated	0.05" thick brass	0.05" thick galvanized steel
	Auto Ground Clip	Brass	Brass	Phosphor bronze
	Line Contacts	0.031" thick 5-leaf brass, nickel plated	5-leaf brass	0.031" thick triple-wipe brass
	Ground Contact	Integral	Integral	Riveted
	Terminal Screws	#8-32 brass, neutral screw nickel plated	#8-32 steel	#8-32 steel, brass plated, neutral screw nickel plated
	Ground Screw	#8-32 brass (green)	#8-32 steel (green)	#8-32 steel, brass plated (green)
	Screw Terminal Guards	PVC hinged doors	PVC hinged doors	N/A
	Illuminated Models	Long-life neon bulb	Long-life neon bulb	N/A