

Specifications



Photo is representative



Eaton C0050E5E

Eaton Type MTE industrial control transformer, 240/480v, taps: none, sv: 23/110v, 24/115v, 25/120v, 55°C, 50 va , pv: 200/220/440v, 208/230/460 v

General specifications

PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0050E5E
UPC	786680420306
PRODUCT LENGTH/DEPTH	3.86 in
PRODUCT HEIGHT	3.26 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	4.3 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified cUL Certified
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

Performance Ratings

PRIMARY VOLTAGE	200/220/440 V, 208/230/460 V, 240/480 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	50 VA
SECONDARY VOLTAGE	23/110 V, 24/115 V, 25/120 V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - C0050E5E
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton C0050E5E

Eaton Type MTE industrial control transformer, 240/480v, taps: none, sv: 23/110v, 24/115v, 25/120v, 55°C, 50 va , pv: 200/220/440v, 208/230/460 v

General specifications

PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0050E5E
UPC	786680420306
PRODUCT LENGTH/DEPTH	3.86 in
PRODUCT HEIGHT	3.26 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	4.3 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified cUL Certified
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

Performance Ratings

PRIMARY VOLTAGE	200/220/440 V, 208/230/460 V, 240/480 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	50 VA
SECONDARY VOLTAGE	23/110 V, 24/115 V, 25/120 V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - C0050E5E
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

