

# Specifications



Photo is representative



## Eaton C0150E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, sv: 120/115/110v, 55°C, 150 va

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0150E2AFB
<b>UPC</b>	786680420863
<b>PRODUCT LENGTH/DEPTH</b>	3.88 in
<b>PRODUCT HEIGHT</b>	4.67 in
<b>PRODUCT WIDTH</b>	3.75 in
<b>PRODUCT WEIGHT</b>	5.3 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CSA Certified UL Listed cUL Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

## Physical Attributes

<b>COIL MATERIAL</b>	Copper windings
<b>DESIGN</b>	MTE
<b>TAP SIZE</b>	None

## Miscellaneous

<b>MODIFICATION 1</b>	Factory-mounted two-pole primary fuse block for non-rejection type fuses
<b>SPECIAL FEATURES</b>	Primary fuse block

## Performance Ratings

<b>PRIMARY VOLTAGE</b>	220 x 440 V, 230 x 460 V, 240 x 480 V
<b>TEMPERATURE RATING</b>	55°C
<b>VOLT AMPERE RATING</b>	150 VA
<b>SECONDARY VOLTAGE</b>	120/115/110 V

## Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - C0150E2AFB</a>
--------------------------------------	--

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton C0150E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, sv: 120/115/110v, 55°C, 150 va

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0150E2AFB
<b>UPC</b>	786680420863
<b>PRODUCT LENGTH/DEPTH</b>	3.88 in
<b>PRODUCT HEIGHT</b>	4.67 in
<b>PRODUCT WIDTH</b>	3.75 in
<b>PRODUCT WEIGHT</b>	5.3 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CSA Certified UL Listed cUL Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes	
COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

Miscellaneous	
MODIFICATION 1	Factory-mounted two-pole primary fuse block for non-rejection type fuses
SPECIAL FEATURES	Primary fuse block

Performance Ratings	
PRIMARY VOLTAGE	220 x 440 V, 230 x 460 V, 240 x 480 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	150 VA
SECONDARY VOLTAGE	120/115/110 V

Resources	
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - C0150E2AFB</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

