



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C0250B 9V Alk Monoxide Alarm

BRK Brands/Ademco/First Alert

Catalog Number	C0250B
Manufacturer	BRK Brands/Ademco/First Alert
Description	Battery Powered CO Alarm With Replaceable Battery and Silence Feature. Includes Electrochemical CO Sensor and 9V Alkaline Battery.
Weight per unit	0.5333 (lbs/each)
Product Category	Smoke & Heat Detectors

Features

alarm type	Audio
dimensions	4.3in x 4.3in x 1.5in
media	Yes
Operating Voltage	9V Alkaline Battery
Output Current	9V Alkaline Battery
Sensor Type	Electrochemical
Temperature Range	40 Degree F (4 Degree C) to 100 Degree F (38 Degree C)

Material, Color, and Finish

Color	White
Enclosure Material	Plastic

Descriptions

Description	9V ALK MONOXIDE ALARM
extra long description	BRK C0250B 9V Battery CO Alarm-BRK
Features	Battery powered CO Alarm with replaceable battery and Silence feature.
Long Description	Battery powered CO Alarm with replaceable battery and Silence feature. Includes electrochemical CO sensor and 9V alkaline battery.
Product Type	9V Battery CO Alarm-BRK

Manufacturer Information

Brand	BRK
GTIN	00029054003928
Manufacturers Part Number	C0250B
UPC	029054003928

Taxonomies, Classifications, and Categories

Category Description	SIGNALING EQUIPMENT
Type	Carbon Monoxide Alarm



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	0.5333

Uses, Certifications, and Standards

Application	Single and or multiple station alarm specifically designed to detect carbon monoxide in residential and institutional applications including sleeping rooms of hospitals, hotels, motels, dormitories and other multi-family dwellings
environmental conditions	10 percent to 90 percent relative humidity (RH)
Mounting	Mount to wall or ceiling
standard	UL2034