



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BGBL10 Lay In Lug #14-1/0, 1/4" Stud Burndy LLC

| | |
|------------------|---|
| Catalog Number | BGBL10 |
| Manufacturer | Burndy LLC |
| Description | Aluminum Lay-In Lug, 1/0-14 Awg, 3/8" Stud, Tin Plated. |
| Weight per unit | 0.0720 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------|----------|
| Hex Size | Slot |
| Material | Aluminum |

Descriptions

| | |
|------------------------|---|
| Description | LAY IN LUG #14-1/0, 1/4" STUD |
| extra long description | BUR BGBL1/0 1/0-14 AL/CU LAY-IN LUG |
| Long Description | Aluminum Lay-in Lug, 1/0-14 AWG, 3/8" Stud, Tin Plated. |
| Product Type | Mechanical |
| Special Features | Features: The Lay-In QIKLUG, Type BGBL Is Manufactured From High Strength 6061-T6 Aluminum, UL486B Listed, AL9CU Rated, For Copper And Aluminum Conductor Combinations Up To 90° C, UL Recognized For Grounding And Bonding, Ensures Reliability, Electro-Tin Plated, Provides Low Contact Resistance, Lay-In Feature, Eases Installation, Stud/bolt Hole Size: 0.28 IN, Dimension D: 0.8 IN, Dimension T: 0.19 IN, Dimension E: 0.83 IN, Dimension K: 0.28 IN, Dimension N: 0.44 IN, Tongue Width: 0.63 IN, Set Screw Type: SI |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | BURNDY |
| GTIN | 00781810124840 |
| Manufacturers Part Number | BGBL1/0 |
| UPC | 781810124840 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | BGBL, Lay-In |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 0.072 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Application | For Copper And Aluminum Conductor Combinations Up To 90 DEG C |
| standard | UL 486A-B |
| Temperature Rating | 194 |