

Eaton C0200E2A

Catalog Number: C0200E2A

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, sv: 120/115/110v, 55°C, 200 va, cu magnet wire

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Type MTE industrial control transformer	C0200E2A
	UPC
	786680422607

Product Length/Depth	Product Height
4.18 in	4.22 in

Product Width	Product Weight
4.5 in	8.9 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	CSA Certified
	cUL Certified
	UL Listed

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material

Copper windings

Design

MTE

Tap size

None

Performance Ratings

Primary voltage

220 x 440 V, 230 x 460 V, 240 x 480 V

Temperature rating

55°C

Volt ampere rating

200 VA

Secondary voltage

120/115/110 V

Resources

Specifications and datasheets

[Eaton Specification Sheet - C0200E2A](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton C0200E2A

Catalog Number: C0200E2A

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, sv: 120/115/110v, 55°C, 200 va, cu magnet wire



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Type MTE industrial control transformer	C0200E2A
	UPC
	786680422607
Product Length/Depth	Product Height
4.18 in	4.22 in
Product Width	Product Weight
4.5 in	8.9 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	CSA Certified
	cUL Certified
	UL Listed

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material

Copper windings

Design

MTE

Tap size

None

Performance Ratings

Primary voltage

220 x 440 V, 230 x 460 V, 240 x 480 V

Temperature rating

55°C

Volt ampere rating

200 VA

Secondary voltage

120/115/110 V

Resources

Specifications and datasheets

[Eaton Specification Sheet - C0200E2A](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)