

Specifications



Photo is representative

Eaton CDR6033

Eaton Crouse-Hinds series PowerMate CDR receptacle, 60A, Three-wire, three-pole, Style 1, Copper-free aluminum, 600 Vac/250 Vdc

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CDR receptacle
CATALOG NUMBER	CDR6033
UPC	662276277243
PRODUCT LENGTH/DEPTH	4.25 in
PRODUCT HEIGHT	4.5 in
PRODUCT WIDTH	4.5 in
PRODUCT WEIGHT	2.2 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

AMPERAGE RATING 60A

	Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X

GROUNDING TYPE	Style 1
CONFIGURATION	Three-wire, three-pole
VOLTAGE RATING	600 Vac/250 Vdc
MATERIAL	Copper-free aluminum

Resources

3D CAD DRAWING PACKAGE [Eaton Crouse-Hinds CDR6033 3D drawing](#)

BROCHURES [PowerMate Drilling Pin and Sleeve Devices brochure](#)

CATALOGS [PowerMate Drilling Pin and Sleeve Devices catalog page](#)

CERTIFICATION REPORTS [PowerMate Drilling Pin and Sleeve Devices UL certification \(Receptacles\)](#)

INSTALLATION INSTRUCTIONS [IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

SPECIFICATIONS AND DATASHEETS [PowerMate Connectors](#)
[Eaton Specification Sheet - CDR6033](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

Reserved.



Specifications



Photo is representative

Eaton CDR6033

Eaton Crouse-Hinds series PowerMate CDR receptacle, 60A, Three-wire, three-pole, Style 1, Copper-free aluminum, 600 Vac/250 Vdc

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CDR receptacle
CATALOG NUMBER	CDR6033
UPC	662276277243
PRODUCT LENGTH/DEPTH	4.25 in
PRODUCT HEIGHT	4.5 in
PRODUCT WIDTH	4.5 in
PRODUCT WEIGHT	2.2 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

AMPERAGE RATING 60A

	Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X

GROUNDING TYPE	Style 1
CONFIGURATION	Three-wire, three-pole
VOLTAGE RATING	600 Vac/250 Vdc
MATERIAL	Copper-free aluminum

Resources

3D CAD DRAWING PACKAGE [Eaton Crouse-Hinds CDR6033 3D drawing](#)

BROCHURES [PowerMate Drilling Pin and Sleeve Devices brochure](#)

CATALOGS [PowerMate Drilling Pin and Sleeve Devices catalog page](#)

CERTIFICATION REPORTS [PowerMate Drilling Pin and Sleeve Devices UL certification \(Receptacles\)](#)

INSTALLATION INSTRUCTIONS [IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

SPECIFICATIONS AND DATASHEETS [PowerMate Connectors](#)
[Eaton Specification Sheet - CDR6033](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

Reserved.

