


Eaton C25DNF240B

Catalog Number: C25DNF240B

Eaton definite purpose contactor, Quick, 40A, 208-240 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 40A, Contactor, 2P, 50A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Non-reversing

General specifications



| | |
|----------------------------------|--------------------------------|
| Product Name | Catalog Number |
| Eaton definite purpose contactor | C25DNF240B |
| UPC | Product Length/Depth |
| 782116300402 | 3.35 in |
| Product Height | Product Width |
| 3.75 in | 2.4 in |
| Product Weight | Warranty |
| 1.19 lb | 1 year |
| Compliances | Certifications |
| RoHS Compliant | UL Recognized CSA Certified |

Product specifications

Amperage Rating

40A

Number Of Poles

Two-pole

Type

Non-reversing

Coil

208-240 Vac

Coil voltage

50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

40 A

Model

Contactors

Resistive load

50 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Connection

Quick

Resources

Drawings

[C25DNF2 2D PDF](#)

[C25DNF2 AutoCAD 2D Footprint](#)

[C25DNF2 AutoCAD 2D Footprint \(mm\)](#)

[C25DNF2 2D Drawing Xchange](#)

[C25DNF2 3D Model Xchange](#)

[C25DNF2 3D Inventor](#)

Specifications and datasheets

[Eaton Specification Sheet - C25DNF240B](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.




[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton C25DNF240B

Catalog Number: C25DNF240B

Eaton definite purpose contactor, Quick, 40A, 208-240 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 40A, Contactor, 2P, 50A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Non-reversing

General specifications



| | |
|----------------------------------|--------------------------------|
| Product Name | Catalog Number |
| Eaton definite purpose contactor | C25DNF240B |
| UPC | Product Length/Depth |
| 782116300402 | 3.35 in |
| Product Height | Product Width |
| 3.75 in | 2.4 in |
| Product Weight | Warranty |
| 1.19 lb | 1 year |
| Compliances | Certifications |
| RoHS Compliant | UL Recognized CSA Certified |

Product specifications

Amperage Rating

40A

Number Of Poles

Two-pole

Type

Non-reversing

Coil

208-240 Vac

Coil voltage

50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

40 A

Model

Contactors

Resistive load

50 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Connection

Quick

Resources

Drawings

[C25DNF2 2D PDF](#)

[C25DNF2 AutoCAD 2D Footprint](#)

[C25DNF2 AutoCAD 2D Footprint \(mm\)](#)

[C25DNF2 2D Drawing Xchange](#)

[C25DNF2 3D Model Xchange](#)

[C25DNF2 3D Inventor](#)

Specifications and datasheets

[Eaton Specification Sheet - C25DNF240B](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)