

# Specifications



## Eaton CH12L125R

Eaton CH main lug loadcenters, Cover included, Main lug only, 125A, B, Copper, NEMA 3R, Metallic, Overhead, CH, 12, 12, Three-wire, Single-phase, 120/240 V, #6-2/0 AWG

### General specifications

<b>PRODUCT NAME</b>	Eaton CH main lug loadcenter
<b>CATALOG NUMBER</b>	CH12L125R
<b>UPC</b>	782113097381
<b>PRODUCT LENGTH/DEPTH</b>	16.75 in
<b>PRODUCT HEIGHT</b>	5.19 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	15.8 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL 50 UL 67
<b>CATALOG NOTES</b>	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

### Product specifications

<b>SPECIAL FEATURES</b>
<b>TYPE</b>
<b>AMPERAGE RATING</b>
<b>BUS MATERIAL</b>
<b>FEED TYPE</b>
<b>MAIN CIRCUIT BREAKER</b>
<b>NUMBER OF CIRCUITS</b>
<b>NUMBER OF SPACES</b>
<b>PHASE</b>
<b>VOLTAGE RATING</b>
<b>WIRE SIZE</b>
<b>BOX SIZE</b>
<b>ENCLOSURE</b>
<b>ENCLOSURE MATERIAL</b>
<b>INTERRUPT RATING</b>
<b>NUMBER OF WIRES</b>



# Specifications



## Eaton CH12L125R

Eaton CH main lug loadcenters, Cover included, Main lug only, 125A, B, Copper, NEMA 3R, Metallic, Overhead, CH, 12, 12, Three-wire, Single-phase, 120/240 V, #6-2/0 AWG

### General specifications

<b>PRODUCT NAME</b>	Eaton CH main lug loadcenter
<b>CATALOG NUMBER</b>	CH12L125R
<b>UPC</b>	782113097381
<b>PRODUCT LENGTH/DEPTH</b>	16.75 in
<b>PRODUCT HEIGHT</b>	5.19 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	15.8 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL 50 UL 67
<b>CATALOG NOTES</b>	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

### Product specifications

<b>SPECIAL FEATURES</b>
<b>TYPE</b>
<b>AMPERAGE RATING</b>
<b>BUS MATERIAL</b>
<b>FEED TYPE</b>
<b>MAIN CIRCUIT BREAKER</b>
<b>NUMBER OF CIRCUITS</b>
<b>NUMBER OF SPACES</b>
<b>PHASE</b>
<b>VOLTAGE RATING</b>
<b>WIRE SIZE</b>
<b>BOX SIZE</b>
<b>ENCLOSURE</b>
<b>ENCLOSURE MATERIAL</b>
<b>INTERRUPT RATING</b>
<b>NUMBER OF WIRES</b>

