

Specifications

Photo is representative

Eaton CDR1034

Eaton Crouse-Hinds series PowerMate CDR receptacle, 100A, Three-wire, four-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CDR receptacle
CATALOG NUMBER	CDR1034
UPC	662276276895
PRODUCT LENGTH/DEPTH	5.25 in
PRODUCT HEIGHT	4.25 in
PRODUCT WIDTH	4.25 in
PRODUCT WEIGHT	2.2 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X

Resources

3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds CDR1034 3D drawing
BROCHURES	PowerMate Drilling Pin and Sleeve Devices brochure
CATALOGS	PowerMate Drilling Pin and Sleeve Devices catalog page
CERTIFICATION REPORTS	PowerMate Drilling Pin and Sleeve Devices UL certification (Receptacles)
INSTALLATION INSTRUCTIONS	IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CDR1034 PowerMate Connectors

Product specifications

AMPERAGE RATING	100A
GROUNDING TYPE	Style 2
CONFIGURATION	Three-wire, four-pole
VOLTAGE RATING	600 Vac/250 Vdc
MATERIAL	Copper-free aluminum

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Photo is representative

Eaton CDR1034

Eaton Crouse-Hinds series PowerMate CDR receptacle, 100A, Three-wire, four-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CDR receptacle
CATALOG NUMBER	CDR1034
UPC	662276276895
PRODUCT LENGTH/DEPTH	5.25 in
PRODUCT HEIGHT	4.25 in
PRODUCT WIDTH	4.25 in
PRODUCT WEIGHT	2.2 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X

Resources

3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds CDR1034 3D drawing
BROCHURES	PowerMate Drilling Pin and Sleeve Devices brochure
CATALOGS	PowerMate Drilling Pin and Sleeve Devices catalog page
CERTIFICATION REPORTS	PowerMate Drilling Pin and Sleeve Devices UL certification (Receptacles)
INSTALLATION INSTRUCTIONS	IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CDR1034 PowerMate Connectors

Product specifications

AMPERAGE RATING	100A
GROUNDING TYPE	Style 2
CONFIGURATION	Three-wire, four-pole
VOLTAGE RATING	600 Vac/250 Vdc
MATERIAL	Copper-free aluminum

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

