

Specifications



Eaton CH20L125C

Eaton CH 3/4-inch loadcenter, single-phase, 20 circuits, 20-pole, #6-2/0 wire, 125Amp, NEMA 1

General specifications

PRODUCT NAME	Eaton CH main lug loadcenter
CATALOG NUMBER	CH20L125C
UPC	782113097572
PRODUCT LENGTH/DEPTH	29.13 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 50 UL 67
CATALOG NOTES	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard.



Powering Business Worldwide

Product specifications

TYPE	Main lug only
AMPERAGE RATING	125 A
BUS MATERIAL	Copper
COVER	Ch8cf-combination, ch8cs-surface
FEED TYPE	Top/bottom
MAIN CIRCUIT BREAKER	CH
NUMBER OF CIRCUITS	20
NUMBER OF SPACES	20
PHASE	Single-phase
WIRE SIZE	#6-2/0 AWG
BOX SIZE	C
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
MULTIMEDIA	AFCI Educational Video
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CH20L125C
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

