



CGB8917 3" NPT Male Cord/Cable Fitting (1.875-2.188)

Crouse-Hinds

Catalog Number	CGB8917
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series CGB Cable Gland, Cable Range Min/Max: 1.875-2.188", Non-Armoured and Tray Cable, Non-Armoured, Steel, General Purpose, 3" NPT
Weight per unit	4.0 (lbs/each)
Product Category	Cable & Cord Grips

Features

connection	Male NPT
dimensions	4.0600 IN X 3.8800 IN X 3.8800 IN
Material	Feraloy Iron Alloy Body and Gland Nut, Neoprene Seal

Material, Color, and Finish

Finish	Electrogalvanized With Aluminum Acrylic Painted
--------	---

Dimensions and Weight

Size	3 in
------	------

Descriptions

Description	3" NPT MALE CORD/CABLE FITTING (1.875-2.188)
extra long description	CRS-H CGB8917 3 CORD/CAB FTG GLAND
Features	They are also listed for use with tray cable types TC, TC-ER, TC-ER-HLA, ITC, ITC-ER, ITC-HL, PLTC and PLTC-ER. When installed in accordance with NEC501.10(B)(4), CGB, CGD, CGE and CGFP non-armoured glands are suitable for use in Class I, Division 2 hazardous locations. Crouse-Hinds series CGB, CGD, CGE and CGFP non-armoured glands are installed to provide a means for passing a cord, unarmoured cable or flexible conduit into an enclosure. The glands form an environmental seal for cord or unarmoured round
Long Description	Eaton Crouse-Hinds series CGB cable gland, Cable range min/max: 1.875-2.188", Non-armoured and tray cable, Non-armoured, Steel, General purpose, 3" NPT
Product Type	3 Cord/Cab FTG Gland Nut Neo Bush
Special Features	Non-Armored Gland, Cord Size 1.875 To 2.188 In



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274773414
Manufacturers Part Number	CGB8917
UPC	782274773414

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland

Packaging

Carton	1
Weight Per each	3.95

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 2
standard	UL (CANADA AND US)
Temperature Rating	-25 To 40 Deg C