

# Specifications



## Eaton CH20L125C

Eaton CH 3/4-inch loadcenter, single-phase, 20 circuits, 20-pole, #6-2/0 wire, 125Amp, NEMA 1

### General specifications

<b>PRODUCT NAME</b>	Eaton CH main lug loadcenter
<b>CATALOG NUMBER</b>	CH20L125C
<b>UPC</b>	782113097572
<b>PRODUCT LENGTH/DEPTH</b>	29.13 in
<b>PRODUCT HEIGHT</b>	3.88 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	15 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL 50 UL 67

### CATALOG NOTES

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard.

### Product specifications

<b>TYPE</b>	Main lug only
<b>AMPERAGE RATING</b>	125 A
<b>BUS MATERIAL</b>	Copper
<b>COVER</b>	Ch8cf-combination, ch8cs-surface
<b>FEED TYPE</b>	Top/bottom
<b>MAIN CIRCUIT BREAKER</b>	CH
<b>NUMBER OF CIRCUITS</b>	20
<b>NUMBER OF SPACES</b>	20
<b>PHASE</b>	Single-phase
<b>WIRE SIZE</b>	#6-2/0 AWG
<b>BOX SIZE</b>	C
<b>ENCLOSURE</b>	NEMA 1
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	25 kAIC
<b>NUMBER OF WIRES</b>	3



Powering Business Worldwide

# Specifications



## Eaton CH20L125C

Eaton CH 3/4-inch loadcenter, single-phase, 20 circuits, 20-pole, #6-2/0 wire, 125Amp, NEMA 1

### General specifications

<b>PRODUCT NAME</b>	Eaton CH main lug loadcenter
<b>CATALOG NUMBER</b>	CH20L125C
<b>UPC</b>	782113097572
<b>PRODUCT LENGTH/DEPTH</b>	29.13 in
<b>PRODUCT HEIGHT</b>	3.88 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	15 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL 50 UL 67

### CATALOG NOTES

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard.

### Product specifications

<b>TYPE</b>	Main lug only
<b>AMPERAGE RATING</b>	125 A
<b>BUS MATERIAL</b>	Copper
<b>COVER</b>	Ch8cf-combination, ch8cs-surface
<b>FEED TYPE</b>	Top/bottom
<b>MAIN CIRCUIT BREAKER</b>	CH
<b>NUMBER OF CIRCUITS</b>	20
<b>NUMBER OF SPACES</b>	20
<b>PHASE</b>	Single-phase
<b>WIRE SIZE</b>	#6-2/0 AWG
<b>BOX SIZE</b>	C
<b>ENCLOSURE</b>	NEMA 1
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	25 kAIC
<b>NUMBER OF WIRES</b>	3



Powering Business Worldwide