

Specifications



Photo is representative



Eaton CH22B125R

Eaton CH main breaker loadcenters, Cover included, Main breaker, 125 A, C, Copper, NEMA 3R, Metallic, 10 kAIC, CH, 22, 22, Three-wire, Single-phase, #6-1/0 AWG, Overhead, 120/240 V

General specifications

PRODUCT NAME	Eaton CH main breaker loadcenter
CATALOG NUMBER	CH22B125R
UPC	782113097640
PRODUCT LENGTH/DEPTH	21 in
PRODUCT HEIGHT	5.19 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15.6 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 50 UL 67
CATALOG NOTES	Furnished with tub hub closure plates for rainproof hubs, refer to page 3-22. Loadcenter contains single insulated/bondable neutral.



Powering Business Worldwide

Product specifications	
SPECIAL FEATURES	Cover included
TYPE	Main breaker
AMPERAGE RATING	125 A
BUS MATERIAL	Copper
MAIN CIRCUIT BREAKER	CH
NUMBER OF CIRCUITS	22
NUMBER OF SPACES	22
PHASE	Single-phase
WIRE SIZE	#6-1/0 AWG
FEED TYPE	Overhead
VOLTAGE RATING	120/240 V
BOX SIZE	C
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

Resources	
CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
MULTIMEDIA	AFCI Educational Video
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CH22B125R
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

