



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH250GFT Type CH 5 Ma GFI BRKR 50A/2 Pole 120/240V 10K_Self

Eaton Corp

Catalog Number	CH250GFT
Manufacturer	Eaton Corp
Description	Ground Fault Circuit Breaker, 50 A, Common Tripping Mechanism, Line and Load Lug Terminal, Plug-On, #14 to #4 Awg Wire Size, 2 In Overall Height, 4.5 In Overall Length, 2.75 In Overall Width, 0.7 LB
Weight per unit	0.8000 (lbs/each)
Product Category	In Circuit Breakers

Features

amperage rating	50 A
connection	Plug-on
dimensions	4.5000 IN X 2.7500 IN X 2.0000 IN
Poles	2
Trip Type	Common
Voltage Rating	120/240 V

Descriptions

Description	TYPE CH 5 MA GFI BRKR 50A/2 POLE 120/240V 10K_SELF
extra long description	ETN CH250GFT CH 5 MA GFI 50A/2 POLE
Special Features	Ground Fault Self Test

Manufacturer Information

Brand	Eaton
GTIN	00786676025652
UPC	786676025652

Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	GFCI circuit breakers

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	10
Weight Per each	0.8



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Marine Vessels and Equipment - Marine Vessels and Equipment -
OtherOtherGeneration - Renewable Energy - Alternative
EnergyGeneration - Conventional Energy - Conventional
EnergyDatacenters - IT Space: CI and Hyper Converged

standard

UL 489