

Eaton CHP60B225X9

Catalog Number: CHP60B225X9

Eaton CH main breaker loadcenters, PON, Main breaker, 225 A, X9, Copper, X9, NEMA 1, Metallic, 25 kAIC, CSR, 120, 60, Three-wire, Single-phase, #2 AWG-300 kcmil, 120/240 V



General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CHP60B225X9
UPC	Product Length/Depth
786679189672	45 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
31 lb	Limited lifetime
Certifications	Catalog Notes
UL 50 UL 67	Purchase Size X9 Cover Separately

Product specifications

Special features

PON

Type

Main breaker

Amperage Rating

225 A

Bus material

Copper

Cover

X9

Main circuit breaker

CSR

Number of circuits

120

Number of spaces

60

Phase

Single-phase

Wire size

#2 AWG-300 kcmil

Voltage rating

120/240 V

Box size

X9

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP60B225X9](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CHP60B225X9

Catalog Number: CHP60B225X9

Eaton CH main breaker loadcenters, PON, Main breaker, 225 A, X9, Copper, X9, NEMA 1, Metallic, 25 kAIC, CSR, 120, 60, Three-wire, Single-phase, #2 AWG-300 kcmil, 120/240 V



General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CHP60B225X9
UPC	Product Length/Depth
786679189672	45 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
31 lb	Limited lifetime
Certifications	Catalog Notes
UL 50 UL 67	Purchase Size X9 Cover Separately

Product specifications

Special features

PON

Type

Main breaker

Amperage Rating

225 A

Bus material

Copper

Cover

X9

Main circuit breaker

CSR

Number of circuits

120

Number of spaces

60

Phase

Single-phase

Wire size

#2 AWG-300 kcmil

Voltage rating

120/240 V

Box size

X9

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP60B225X9](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)