



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHQ150 Type CHQ Classified BRKR 50A/1 Pole 120/240V 10K

*Eaton Corp*

Catalog Number	CHQ150
Manufacturer	Eaton Corp
Description	3/4" Thermal Magnetic Circuit Breakers, Type CHQ 3/4-Inch Classified Replacement Breaker Clamshell Pack, Ground Fault, 50 A, 10 Kaic, Single-Pole, 120/240V, CHQ, (1) #14-8 Awg, (2) #14-10 Awg Cu/Al, Q30, CHQ, Type CH Loadcenters
Weight per unit	0.3000 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

### Features

amps	50
dimensions	2.5000 IN X 0.8000 IN X 3.0000 IN
interrupt rating	10
pole	Single
Poles	1
Voltage Rating	120/240 V

### Descriptions

Description	TYPE CHQ CLASSIFIED BRKR 50A/1 POLE 120/240V 10K
extra long description	ETN CHQ150 CHQ Classified 50A/1 Pol
Features	Eaton UL classified replacement circuit breakers are available in both 3/4-inch Type CHQ and 1-inch Type CL, single- and two-pole configurations. These breakers are classified as direct replacements by Underwriters Laboratories. In addition to a UL listing, they also come with a 15-year warranty.
Long Description	3/4" Thermal magnetic circuit breakers, Type CHQ 3/4-Inch classified replacement breaker clamshell pack, Ground fault, 50 A, 10 kAIC, Single-pole, 120/240V, CHQ, (1) #14-8 AWG, (2) #14-10 AWG Cu/Al, Q30, CHQ, Type CH Loadcenters
Product Type	CHQ Classified 50A/1 Pole 120/240V 10K
Special Features	Ground fault

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113010885
Manufacturers Part Number	CHQ150
UPC	782113010885

### Taxonomies, Classifications, and Categories

Category Description	CLASSIFIED BREAKERS
Type	3/4" Thermal magnetic circuit breakers



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	20
Package	100
Weight Per each	0.3

## Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative Energy Generation - Conventional Energy - Conventional Energy Datacenters - IT Space: CI and Hyper Converged Marine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489