

# Eaton CHU7N7N5GS

Catalog Number: CHU7N7N5GS

Eaton pedestal mount unmetered, Unmetered, 20A, 20A, 20A, Non-ground fault, Non-ground fault, Ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 5-20R2GFI, NEMA 6-20R2, 3, 3, 3, 125V, 125V, 250V



## General specifications

### Product Name

Eaton pedestal mount unmetered

### Catalog Number

CHU7N7N5GS

### UPC

782114215753

### Product Length/Depth

4.3 in

### Product Height

17.1 in

### Product Width

9.5 in

### Product Weight

26 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed file E163588

UL 231

## Physical Attributes

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

Ground fault

### Feed type

Top

### Mounting

Surface

### Number of circuits

4

### Receptacle center

NEMA 5-20R2GFI

### Receptacle left

NEMA 5-20R2GFI

### Receptacle right

NEMA 6-20R2

### Type

Unmetered

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHU7N7N5GS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton CHU7N7N5GS

Catalog Number: CHU7N7N5GS

Eaton pedestal mount unmetered, Unmetered, 20A, 20A, 20A, Non-ground fault, Non-ground fault, Ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 5-20R2GFI, NEMA 6-20R2, 3, 3, 3, 125V, 125V, 250V

## General specifications



### Product Name

Eaton pedestal mount unmetered

### Catalog Number

CHU7N7N5GS

### UPC

782114215753

### Product Length/Depth

4.3 in

### Product Height

17.1 in

### Product Width

9.5 in

### Product Weight

26 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed file E163588

UL 231

## Physical Attributes

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

Ground fault

### Feed type

Top

### Mounting

Surface

### Number of circuits

4

### Receptacle center

NEMA 5-20R2GFI

### Receptacle left

NEMA 5-20R2GFI

### Receptacle right

NEMA 6-20R2

### Type

Unmetered

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHU7N7N5GS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)