

Specifications

Eaton CHU7N7N5GS

Eaton pedestal mount unmetered,
Unmetered, 20A, 20A, 20A, Non-ground
fault, Non-ground fault, Ground fault, Top,
Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA
5-20R2GFI, NEMA 6-20R2, 3, 3, 3, 125V, 125V,
250V

General specifications

PRODUCT NAME	Eaton pedestal mount unmetered
CATALOG NUMBER	CHU7N7N5GS
UPC	782114215753
PRODUCT LENGTH/DEPTH	4.3 in
PRODUCT HEIGHT	17.1 in
PRODUCT WIDTH	9.5 in
PRODUCT WEIGHT	26 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed file E163588 UL 231

Physical Attributes

CIRCUIT BREAKER POSITION 1	Non-ground fault
-----------------------------------	------------------

CIRCUIT BREAKER POSITION 2	Non-ground fault
-----------------------------------	------------------

CIRCUIT BREAKER POSITION 3	Ground fault
-----------------------------------	--------------

FEED TYPE	Top
------------------	-----

MOUNTING	Surface
-----------------	---------

NUMBER OF CIRCUITS	4
---------------------------	---

RECEPTACLE CENTER	NEMA 5-20R2GFI
--------------------------	----------------

RECEPTACLE LEFT	NEMA 5-20R2GFI
------------------------	----------------

RECEPTACLE RIGHT	NEMA 6-20R2
-------------------------	-------------

TYPE	Unmetered
-------------	-----------

Resources

CATALOGS	Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5
-----------------	---

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHU7N7N5GS
--------------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton CHU7N7N5GS

Eaton pedestal mount unmetered,
Unmetered, 20A, 20A, 20A, Non-ground
fault, Non-ground fault, Ground fault, Top,
Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA
5-20R2GFI, NEMA 6-20R2, 3, 3, 3, 125V, 125V,
250V

General specifications

PRODUCT NAME	Eaton pedestal mount unmetered
CATALOG NUMBER	CHU7N7N5GS
UPC	782114215753
PRODUCT LENGTH/DEPTH	4.3 in
PRODUCT HEIGHT	17.1 in
PRODUCT WIDTH	9.5 in
PRODUCT WEIGHT	26 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed file E163588 UL 231

Physical Attributes

CIRCUIT BREAKER POSITION 1	Non-ground fault
-----------------------------------	------------------

CIRCUIT BREAKER POSITION 2	Non-ground fault
-----------------------------------	------------------

CIRCUIT BREAKER POSITION 3	Ground fault
-----------------------------------	--------------

FEED TYPE	Top
------------------	-----

MOUNTING	Surface
-----------------	---------

NUMBER OF CIRCUITS	4
---------------------------	---

RECEPTACLE CENTER	NEMA 5-20R2GFI
--------------------------	----------------

RECEPTACLE LEFT	NEMA 5-20R2GFI
------------------------	----------------

RECEPTACLE RIGHT	NEMA 6-20R2
-------------------------	-------------

TYPE	Unmetered
-------------	-----------

Resources

CATALOGS	Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5
-----------------	---

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHU7N7N5GS
--------------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

