

Service Entrance Splices

Standard 2" length compression splices.

Aluminum Service Entrance Compression Splices — U 1 B™ and CS™ 5/8" Die Series

- Constructed from aluminum for high conductivity
- Solid center barriers and large chamfers for easy cable insertion
- Prefilled with oxide inhibitor to prevent oxidation and keep out moisture
- All splices are color coded and marked with strip lengths, installation die codes and compression locations, providing easy identification for easy installation
- Comply with ANSI C119.4 when properly installed on aluminum-to-aluminum or aluminum-to-copper conductors
- RUS Accepted



U 1 B 1010 EC



CS73


| U 1 B SERIES CAT. NO. | CS SERIES CAT. NO. | CONDUCTOR A | | | | CONDUCTOR B | | | |
|--------------------------|-----------------------|-------------|---------------|---------|------|-------------|---------------|---------|------|
| | | COLOR | ACSR | STR. | SOL. | COLOR | ACSR | STR. | SOL. |
| U 1 B 11 | — | BROWN | — | #10 | #8 | BROWN | — | #10 | #8 |
| U 1 B 88 | CS61 | GREEN | — | #8 | #6 | GREEN | — | #8 | #6 |
| U 1 B 81 | — | BLUE | #6 (6/1) | — | #4 | BROWN | — | #10 | #8 |
| U 1 B 66 | CS64 | | | | | BLUE | #6 (6/1) | — | #4 |
| U 1 B 68 | CS63 | | | | | GREEN | — | #8 | #6 |
| U 1 B 61 | CS62 | | | | | BROWN | — | #10 | #8 |
| U 1 B 612 | — | ORANGE | #4 (6/1, 7/1) | — | #2 | BLACK | — | #12 | #10 |
| U 1 B 44 | CS68 | | | | | ORANGE | #4 (6/1, 7/1) | — | #2 |
| U 1 B 46 | CS67 | | | | | BLUE | #6 (6/1) | — | #4 |
| U 1 B 48 | CS66 | | | | | GREEN | — | #8 | #6 |
| U 1 B 41 | CS65 | BROWN | — | #10 | #8 | | | | |
| U 1 B 22 | CS73 | RED | #2 (6/1, 7/1) | #1 & #2 | #1 | RED | #2 (6/1, 7/1) | #1 & #2 | #1 |
| U 1 B 24 | CS72 | | | | | ORANGE | #4 (6/1, 7/1) | — | #2 |
| U 1 B 26 | CS71 | | | | | BLUE | #6 (6/1) | — | #4 |
| U 1 B 28 | CS70 | | | | | GREEN | — | #8 | #6 |
| U 1 B 21 | CS69 | BROWN | — | #10 | #8 | | | | |
| U 1 B 1010 | CS78 | YELLOW | 1/0 (6/1) | 1/0 | #1 | YELLOW | 1/0 (6/1) | 1/0 | — |
| U 1 B 102 | CS77 | | | | | RED | #2 (6/1, 7/1) | #1 & #2 | #1 |
| U 1 B 104 | CS76 | | | | | ORANGE | #4 (6/1, 7/1) | — | #2 |
| U 1 B 106 | CS75 | | | | | BLUE | #6 (6/1) | — | #4 |
| U 1 B 108 | CS74 | GREEN | — | #8 | #6 | | | | |
| — | CS84 | GRAY | — | 2/0 | — | YELLOW | 1/0 (6/1) | 1/0 | — |
| — | CS85 | | | | | GRAY | — | 2/0 | — |

Service Entrance Splices

Standard 2" length compression splices.

Aluminum Service Entrance Compression Splices — U 1 B™ and CS™ 5/8" Die Series

- Constructed from aluminum for high conductivity
- Solid center barriers and large chamfers for easy cable insertion
- Prefilled with oxide inhibitor to prevent oxidation and keep out moisture
- All splices are color coded and marked with strip lengths, installation die codes and compression locations, providing easy identification for easy installation
- Comply with ANSI C119.4 when properly installed on aluminum-to-aluminum or aluminum-to-copper conductors
- RUS Accepted



U 1 B 1010 EC



CS73

| U 1 B SERIES CAT. NO. | CS SERIES CAT. NO. | CONDUCTOR A | | | | CONDUCTOR B | | | |
|--------------------------|-----------------------|-------------|---------------|---------|------|---------------|---------------|---------|------|
| | | COLOR | ACSR | STR. | SOL. | COLOR | ACSR | STR. | SOL. |
| U 1 B 11 | — | BROWN | — | #10 | #8 | BROWN | — | #10 | #8 |
| U 1 B 88 | CS61 | GREEN | — | #8 | #6 | GREEN | — | #8 | #6 |
| U 1 B 81 | — | BLUE | #6 (6/1) | — | #4 | BROWN | — | #10 | #8 |
| U 1 B 66 | CS64 | | | | | BLUE | #6 (6/1) | — | #4 |
| U 1 B 68 | CS63 | | | GREEN | — | #8 | #6 | | |
| U 1 B 61 | CS62 | | | BROWN | — | #10 | #8 | | |
| U 1 B 612 | — | ORANGE | #4 (6/1, 7/1) | 6 | #2 | BLACK | — | #12 | #10 |
| U 1 B 44 | CS68 | | | ORANGE | | #4 (6/1, 7/1) | — | #2 | |
| U 1 B 46 | CS67 | | | BLUE | | #6 (6/1) | — | #4 | |
| U 1 B 48 | CS66 | | | GREEN | | — | #8 | #6 | |
| U 1 B 41 | CS65 | BROWN | — | #10 | #8 | | | | |
| U 1 B 22 | CS73 | RED | #2 (6/1, 7/1) | #1 & #2 | #1 | RED | #2 (6/1, 7/1) | #1 & #2 | #1 |
| U 1 B 24 | CS72 | | | | | ORANGE | #4 (6/1, 7/1) | — | #2 |
| U 1 B 26 | CS71 | | | | | BLUE | #6 (6/1) | — | #4 |
| U 1 B 28 | CS70 | | | | | GREEN | — | #8 | #6 |
| U 1 B 21 | CS69 | BROWN | — | #10 | #8 | | | | |
| U 1 B 1010 | CS78 | YELLOW | 1/0 (6/1) | 1/0 | #1 | YELLOW | 1/0 (6/1) | 1/0 | — |
| U 1 B 102 | CS77 | | | | | RED | #2 (6/1, 7/1) | #1 & #2 | #1 |
| U 1 B 104 | CS76 | | | | | ORANGE | #4 (6/1, 7/1) | — | #2 |
| U 1 B 106 | CS75 | | | | | BLUE | #6 (6/1) | — | #4 |
| U 1 B 108 | CS74 | GREEN | — | #8 | #6 | | | | |
| — | CS84 | GRAY | — | 2/0 | — | YELLOW | 1/0 (6/1) | 1/0 | — |
| — | CS85 | | | | | GRAY | — | 2/0 | — |