

# Specifications

## Eaton CS8365EX

Eaton locking plug, #10-6 AWG, 50A, Industrial, 250V, Back wiring, Black, red, Non-NEMA, Three-pole, Four-wire, Nylon, 0.44 to 1.06 in, California standard

### General specifications

<b>PRODUCT NAME</b>	Eaton Arrow Hart pro grip California standard locking plug
<b>CATALOG NUMBER</b>	CS8365EX
<b>UPC</b>	032664663949
<b>PRODUCT LENGTH/DEPTH</b>	6.94 in
<b>PRODUCT HEIGHT</b>	3.38 in
<b>PRODUCT WIDTH</b>	3.61 in
<b>PRODUCT WEIGHT</b>	1.05 lb
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	cULus Listed
<b>PRODUCT TYPE</b>	Pro grip California standard



Powering Business Worldwide

## Product specifications

<b>SPECIAL FEATURES</b>	Locking plug
<b>TYPE</b>	Locking plug
<b>AMPERAGE RATING</b>	50 A
<b>VOLTAGE RATING</b>	3Ø 250 V
<b>CONTACT MATERIAL</b>	Zinc plated brass
<b>APPLICATION</b>	Industrial
<b>DEVICE GRADE</b>	Extra heavy duty
<b>WIRING METHOD</b>	Back
<b>NUMBER OF WIRES</b>	4 Grounding
<b>NUMBER OF POLES</b>	Three-pole
<b>COLOR</b>	Red Black
<b>CORD DIAMETER</b>	0.44-1.06 in (11.1-26.0 mm)
<b>MATERIAL</b>	Nylon
<b>OPERATING TEMPERATURE</b>	-40 to 105 °C (-40 to 221 °F)
<b>STANDARD</b>	California standard
<b>ALLOWABLE WIRE SIZE</b>	#10-4 AWG
<b>NEMA CONFIGURATION</b>	Non-NEMA
<b>TORQUE RATING</b>	45 lbf-inch
<b>DESIGN TYPE</b>	Pro grip
<b>FACE/BODY MATERIAL</b>	Glass filled nylon

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

## Resources

MULTIMEDIA	<a href="#">Arrow Hart - Connecting Safety to Reliability since 1890</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Hart lock industrial grade 50A locking devices spec sheet</a> <a href="#">Eaton Specification Sheet - CS8365EX</a> <a href="#">Industrial grade 50A locking devices spec sheet</a>



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

