



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CM Power Dist Block Cover For "Am" Series

*Nsi Industries*

Catalog Number	CM
Manufacturer	Nsi Industries
Description	Medium Power Distribution Block Cover Medium Power Distribution Block Covers Are See Through, Clear Acrylic Covers to Permit Visual Inspection. Snaps Easily Into Place. For Use With Connector Blocks Series With Prefix Am.
Weight per unit	0.0400 (lbs/each)
Product Category	Terminal Blocks & Accessories

### Features

Material	Clear Acrylic
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Clear
Finish	Acrylic

### Dimensions and Weight

Size	Medium Cover
------	--------------

### Descriptions

Description	POWER DIST BLOCK COVER FOR "AM" SERIES
extra long description	NSI CM MEDIUM POWER DISTRIBUTION C
Features	Medium Power Distribution Block Cover Medium power distribution block covers are see through, clear acrylic covers to permit visual inspection. Snaps easily into place. For use with connector blocks series with prefix AM.
Long Description	Medium Power Distribution Block Cover Medium power distribution block covers are see through, clear acrylic covers to permit visual inspection. Snaps easily into place. For use with connector blocks series with prefix AM.
Product Type	Medium Power Distribution Cover
Special Features	For use with Medium Connector Blocks - # 9 Bolt Size

### Manufacturer Information

Brand	NSi
GTIN	00662381166265
UPC	662381166265

### Taxonomies, Classifications, and Categories

Category Description	TERMINAL BLOCKS POWER DIST BLOCKS
Type	Covers



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	9
Weight Per each	0.04

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Temperature Rating	90 C