

## DESCRIPTION

The DMF Series is an energy efficient family of industrials that feature premium performance and durability. The industrial series incorporates heavy duty, embossed, reflectors that precisely direct and effectively control light. The versatile DMF Series can be installed using various mounting methods, and numerous options and accessories are available.

The DMF Series can be utilized in simple task and area lighting to the most demanding industrial applications.

| Catalog #   |  | Type |
|-------------|--|------|
| Project     |  |      |
| Comments    |  | Date |
| Prepared by |  |      |

## SPECIFICATION FEATURES

### Construction

Channel is code gauge prime cold rolled steel. Die formed with deep V-grooves for tong hanger. Die formed channel connector assures straight rows and continuity of ground through set screws. Lampholder mounting brackets are easily inserted with snap-in action.

### Electrical\*

Ballast are CBM/ETL Class "P" and positively secured by mounting bolts. Metal clad lampholders are spring loaded for turret safety. UL/cUL listed. Suitable for damp locations.

### Finish

Multistage iron phosphate pre-treatment ensures maximum bonding and rust inhibitor. Lighting grade, baked white enamel finish.

### Reflectors


Die formed prime steel, code gauge. Deep draw full width ribs formed with one press stroke. Side flanges lend strength with upward turn. Easily cleaned. Baked white enamel 13-1/2" width. Four foot sections. Reflectors secured by positive retaining screw. Reflector aligners provided. Standard with 20% uplight (DMF). Closed top reflector (DCMF). Optional industrial fixtures are available incorporating silver technology enhancements (SilverLining).




**DMF**  
232  
332  
432

4' OR 8' INDUSTRIAL  
2, 3 OR 4 LAMP


Heavy Duty Industrial



## LAMP CONFIGURATIONS



## MOUNTING DATA



## ENERGY DATA

Input Watts:  
ES Ballast & STD Lamps  
232 (71), 332 (108), 432 (142)

Luminaire Efficacy Rating  
LER = FI-78  
Catalog Number: DMF-232

Yearly Cost of 1000 lumens, 3000  
hrs at .08 KWH = \$3.08

\*Reference the lamp/ballast data in the  
Technical Section for specific lamp/ballast  
requirements.


LAMPS CONTAIN MERCURY. DISPOSE ACCORDING  
TO LOCAL, STATE OR FEDERAL LAWS

**LINEAR DISCONNECT**

Safe and convenient means of  
disconnecting power.



PHOTOMETRICS



**DMF-232**  
Electronic Ballast  
F32T8/35K Lamps  
2850 Lumens  
Spacing criterion:  
(H) 1.3 x mounting  
height, (L) 1.4 x  
mounting height  
Efficiency 90.8%  
Test Report:  
DMF232.IES  
LER = FI-78  
Yearly Cost of 1000  
lumens, 3000 hrs at  
.08 KWH = \$3.08

Coefficients of Utilization

| Effective floor cavity reflectance |     |     |     |     |     |     |     |     | 20% |    |    |    |     |    |    |    |     |    |  |  |    |  |  |  |  |  |
|------------------------------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|----|----|----|-----|----|--|--|----|--|--|--|--|--|
| rc                                 | 80% |     |     |     | 70% |     |     |     | 50% |    |    |    | 30% |    |    |    | 10% |    |  |  | 0% |  |  |  |  |  |
| rw                                 | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30 | 10 | 50 | 30  | 10 | 50 | 30 | 10  | 0  |  |  |    |  |  |  |  |  |
| RCR                                |     |     |     |     |     |     |     |     |     |    |    |    |     |    |    |    |     |    |  |  |    |  |  |  |  |  |
| 0                                  | 105 | 105 | 105 | 105 | 100 | 100 | 100 | 100 | 93  | 93 | 93 | 86 | 86  | 86 | 79 | 79 | 79  | 76 |  |  |    |  |  |  |  |  |
| 1                                  | 95  | 91  | 87  | 84  | 91  | 88  | 84  | 81  | 81  | 78 | 76 | 75 | 73  | 71 | 70 | 68 | 66  | 64 |  |  |    |  |  |  |  |  |
| 2                                  | 87  | 79  | 73  | 68  | 83  | 76  | 71  | 66  | 71  | 66 | 62 | 66 | 62  | 59 | 61 | 58 | 55  | 53 |  |  |    |  |  |  |  |  |
| 3                                  | 79  | 70  | 62  | 57  | 76  | 67  | 61  | 55  | 62  | 57 | 52 | 58 | 53  | 50 | 54 | 50 | 47  | 44 |  |  |    |  |  |  |  |  |
| 4                                  | 72  | 61  | 54  | 48  | 69  | 59  | 52  | 47  | 55  | 49 | 44 | 51 | 46  | 42 | 48 | 44 | 40  | 38 |  |  |    |  |  |  |  |  |
| 5                                  | 66  | 54  | 46  | 40  | 63  | 52  | 45  | 39  | 49  | 42 | 37 | 45 | 40  | 35 | 42 | 37 | 34  | 31 |  |  |    |  |  |  |  |  |
| 6                                  | 60  | 48  | 40  | 34  | 57  | 46  | 39  | 33  | 43  | 37 | 32 | 40 | 35  | 30 | 38 | 33 | 29  | 27 |  |  |    |  |  |  |  |  |
| 7                                  | 55  | 43  | 35  | 29  | 53  | 42  | 34  | 29  | 39  | 32 | 28 | 36 | 31  | 26 | 34 | 29 | 25  | 23 |  |  |    |  |  |  |  |  |
| 8                                  | 51  | 38  | 31  | 25  | 49  | 37  | 30  | 25  | 35  | 28 | 24 | 32 | 27  | 23 | 30 | 25 | 22  | 20 |  |  |    |  |  |  |  |  |
| 9                                  | 47  | 34  | 27  | 22  | 45  | 33  | 26  | 21  | 31  | 25 | 20 | 29 | 23  | 19 | 27 | 22 | 19  | 17 |  |  |    |  |  |  |  |  |
| 10                                 | 43  | 31  | 24  | 19  | 41  | 30  | 23  | 19  | 28  | 22 | 18 | 26 | 21  | 17 | 25 | 20 | 16  | 15 |  |  |    |  |  |  |  |  |

Zonal Lumen Summary

| Zone          | Lumens | %Lamp | %Fixture |
|---------------|--------|-------|----------|
| <b>0-30</b>   | 1016   | 17.8  | 19.6     |
| <b>0-40</b>   | 1703   | 29.9  | 32.9     |
| <b>0-60</b>   | 3238   | 56.8  | 62.5     |
| <b>0-90</b>   | 4330   | 76.0  | 83.7     |
| <b>90-180</b> | 846    | 14.8  | 16.3     |
| <b>0-180</b>  | 5176   | 90.8  | 100.0    |

Candela

| Angle      | Along H | 45°  | Across L |
|------------|---------|------|----------|
| <b>0</b>   | 1278    | 1278 | 1278     |
| <b>10</b>  | 1258    | 1264 | 1268     |
| <b>20</b>  | 1195    | 1214 | 1228     |
| <b>30</b>  | 1092    | 1133 | 1180     |
| <b>40</b>  | 952     | 1039 | 1174     |
| <b>50</b>  | 781     | 972  | 1075     |
| <b>60</b>  | 582     | 817  | 724      |
| <b>70</b>  | 367     | 472  | 553      |
| <b>80</b>  | 157     | 251  | 138      |
| <b>90</b>  | 15      | 30   | 21       |
| <b>100</b> | 31      | 65   | 50       |
| <b>110</b> | 96      | 18   | 38       |
| <b>120</b> | 169     | 45   | 20       |
| <b>130</b> | 240     | 140  | 64       |
| <b>140</b> | 304     | 244  | 173      |
| <b>150</b> | 358     | 286  | 286      |
| <b>160</b> | 398     | 369  | 311      |
| <b>170</b> | 424     | 426  | 420      |
| <b>180</b> | 434     | 434  | 434      |

ORDERING INFORMATION

SAMPLE NUMBER: DMF-232-120V-EB81-U

|                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                                                                                                                                                                                  |                                                                                                                                                                                                                                                       |                                              |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------|
| <b>Tandem</b><br>Blank=4' Length<br>8T=8' Length<br><br><b>Series</b><br>DMF= Apertured Reflector<br>DCMF= Closed Top Reflector<br><br><b>Lamp Spacing</b><br>Blank=Standard Spacing<br>N=Narrow Spacing for 2 Lamp Only (10% uplight) | <b>Number of Lamps</b><br>2, 3 or 4<br>Lamps (Not included)<br><br><b>Wattage (Length)</b><br>32=32W T8 (48")<br><br><b>Voltage <sup>(1)</sup></b><br>120V=120 Volt<br>277V=277 Volt<br>347V=347 Volt<br>UNV=Universal Voltage 120-277<br><br><b>Options</b><br>GL=Single Element Fuse<br>GM=Double Element Fuse<br>EL=Emergency Installed | <b>Ballast Type <sup>(1)</sup></b><br>EB8 =T8 Electronic Instant Start.<br>Total Harmonic Distortion < 10%<br>No. of Ballast<br>1, 2 or 3<br>EB8 /PLUS=T8 Electronic Instant Start.<br>High Ballast Factor >1.13.<br>Total Harmonic Distortion < 20%<br>No. of Ballast<br>1, 2 or 3<br>ER8 =T8 Electronic Program Rapid Start.<br>Total Harmonic Distortion < 10%<br>No. of Ballast<br>1, 2 or 3 | <b>Options</b><br>6-3/18 SJT-C&P-515P=Cord & Plug (120V)<br>6-3/18 SJT-C&P-L715P=Cord & Plug (277V)<br>PI/CPI=Plug-In Option<br>TILW=Tandem In-Line Wiring Option (Consult TILW Option Catalog Page)<br>POX=Porlux Finish (See options & accessories) | <b>Packaging</b><br>U=Unit Pack<br>4B=4 Bulk |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------|

ACCESSORIES

(Order Separately)

**A1B/Spacer-U**=Spacer 1-1/2" to 2-1/2" from ceiling (Use 2 per fixture)

**ATG-DIF-4-U**=Tong Hanger (Use 2 per fixture)

**SCF**=Fixed Stem Set (Specify Length)

**SCS**=Swivel Stem Set (Specify Length)

**SCA**=Adjustable 48" Stem Set

**AYC-Chain/Set-U**=Chain Hanger Set (Use 1 set per fixture)

**WG/DIF4FT-U**=Wire Guard

**GYM GUARD, GG-DIF**=Wire Gym Guard

**MECL-DIF/RS-49-3/4-U**=Metal Egg Crate Louver

**MECL-DIF/RS-99-1/2-U**=Metal Egg Crate Louver

**DIF2 LONG CONN (PREPAINTED)**=Long Connector

**DIF CLOSED END PLATE**=Closed End Plate

SHIPPING DATA

| Catalog No. | Wt.     |
|-------------|---------|
| DMF-232     | 15 lbs. |
| 8TDMF-232   | 30 lbs. |
| DMF-332     | 25 lbs. |
| DMF-432     | 25 lbs. |

NOTES: <sup>(1)</sup>Products also available in non-US voltages and frequencies for international markets.

Specifications & dimensions subject to change without notice. Consult your Cooper Lighting Representative for availability and ordering information.

## DESCRIPTION

The DMF Series is an energy efficient family of industrials that feature premium performance and durability. The industrial series incorporates heavy duty, embossed, reflectors that precisely direct and effectively control light. The versatile DMF Series can be installed using various mounting methods, and numerous options and accessories are available.

The DMF Series can be utilized in simple task and area lighting to the most demanding industrial applications.

| Catalog #   |  | Type |
|-------------|--|------|
| Project     |  |      |
| Comments    |  | Date |
| Prepared by |  |      |

## SPECIFICATION FEATURES

### Construction

Channel is code gauge prime cold rolled steel. Die formed with deep V-grooves for tong hanger. Die formed channel connector assures straight rows and continuity of ground through set screws. Lampholder mounting brackets are easily inserted with snap-in action.

### Electrical\*

Ballast are CBM/ETL Class "P" and positively secured by mounting bolts. Metal clad lampholders are spring loaded for turret safety. UL/cUL listed. Suitable for damp locations.

### Finish

Multistage iron phosphate pre-treatment ensures maximum bonding and rust inhibitor. Lighting grade, baked white enamel finish.

### Reflectors


Die formed prime steel, code gauge. Deep draw full width ribs formed with one press stroke. Side flanges lend strength with upward turn. Easily cleaned. Baked white enamel 13-1/2" width. Four foot sections. Reflectors secured by positive retaining screw. Reflector aligners provided. Standard with 20% uplight (DMF). Closed top reflector (DCMF). Optional industrial fixtures are available incorporating silver technology enhancements (SilverLining).




**DMF**  
232  
332  
432

4' OR 8' INDUSTRIAL  
2, 3 OR 4 LAMP


Heavy Duty Industrial



## LAMP CONFIGURATIONS



## MOUNTING DATA



## ENERGY DATA

Input Watts:  
**ES Ballast & STD Lamps**  
232 (71), 332 (108), 432 (142)

Luminaire Efficacy Rating  
**LER = FI-78**  
Catalog Number: DMF-232

Yearly Cost of 1000 lumens, 3000  
hrs at .08 KWH = \$3.08

\*Reference the lamp/ballast data in the  
Technical Section for specific lamp/ballast  
requirements.


**LAMPS CONTAIN MERCURY. DISPOSE ACCORDING  
TO LOCAL, STATE OR FEDERAL LAWS**

**LINEAR DISCONNECT**

Safe and convenient means of  
disconnecting power.



PHOTOMETRICS



**DMF-232**  
Electronic Ballast  
F32T8/35K Lamps  
2850 Lumens  
Spacing criterion:  
(H) 1.3 x mounting  
height, (L) 1.4 x  
mounting height  
Efficiency 90.8%  
Test Report:  
DMF232.IES  
LER = FI-78  
Yearly Cost of 1000  
lumens, 3000 hrs at  
.08 KWH = \$3.08

Coefficients of Utilization

| Effective floor cavity reflectance |     |     |     |     |     |     |     |     | 20% |    |    |    |     |    |    |    |     |    |  |  |    |  |  |  |  |  |
|------------------------------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|----|----|----|-----|----|--|--|----|--|--|--|--|--|
| rc                                 | 80% |     |     |     | 70% |     |     |     | 50% |    |    |    | 30% |    |    |    | 10% |    |  |  | 0% |  |  |  |  |  |
| rw                                 | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30 | 10 | 50 | 30  | 10 | 50 | 30 | 10  | 0  |  |  |    |  |  |  |  |  |
| RCR                                |     |     |     |     |     |     |     |     |     |    |    |    |     |    |    |    |     |    |  |  |    |  |  |  |  |  |
| 0                                  | 105 | 105 | 105 | 105 | 100 | 100 | 100 | 100 | 93  | 93 | 93 | 86 | 86  | 86 | 79 | 79 | 79  | 76 |  |  |    |  |  |  |  |  |
| 1                                  | 95  | 91  | 87  | 84  | 91  | 88  | 84  | 81  | 81  | 78 | 76 | 75 | 73  | 71 | 70 | 68 | 66  | 64 |  |  |    |  |  |  |  |  |
| 2                                  | 87  | 79  | 73  | 68  | 83  | 76  | 71  | 66  | 71  | 66 | 62 | 66 | 62  | 59 | 61 | 58 | 55  | 53 |  |  |    |  |  |  |  |  |
| 3                                  | 79  | 70  | 62  | 57  | 76  | 67  | 61  | 55  | 62  | 57 | 52 | 58 | 53  | 50 | 54 | 50 | 47  | 44 |  |  |    |  |  |  |  |  |
| 4                                  | 72  | 61  | 54  | 48  | 69  | 59  | 52  | 47  | 55  | 49 | 44 | 51 | 46  | 42 | 48 | 44 | 40  | 38 |  |  |    |  |  |  |  |  |
| 5                                  | 66  | 54  | 46  | 40  | 63  | 52  | 45  | 39  | 49  | 42 | 37 | 45 | 40  | 35 | 42 | 37 | 34  | 31 |  |  |    |  |  |  |  |  |
| 6                                  | 60  | 48  | 40  | 34  | 57  | 46  | 39  | 33  | 43  | 37 | 32 | 40 | 35  | 30 | 38 | 33 | 29  | 27 |  |  |    |  |  |  |  |  |
| 7                                  | 55  | 43  | 35  | 29  | 53  | 42  | 34  | 29  | 39  | 32 | 28 | 36 | 31  | 26 | 34 | 29 | 25  | 23 |  |  |    |  |  |  |  |  |
| 8                                  | 51  | 38  | 31  | 25  | 49  | 37  | 30  | 25  | 35  | 28 | 24 | 32 | 27  | 23 | 30 | 25 | 22  | 20 |  |  |    |  |  |  |  |  |
| 9                                  | 47  | 34  | 27  | 22  | 45  | 33  | 26  | 21  | 31  | 25 | 20 | 29 | 23  | 19 | 27 | 22 | 19  | 17 |  |  |    |  |  |  |  |  |
| 10                                 | 43  | 31  | 24  | 19  | 41  | 30  | 23  | 19  | 28  | 22 | 18 | 26 | 21  | 17 | 25 | 20 | 16  | 15 |  |  |    |  |  |  |  |  |

Zonal Lumen Summary

| Zone          | Lumens | %Lamp | %Fixture |
|---------------|--------|-------|----------|
| <b>0-30</b>   | 1016   | 17.8  | 19.6     |
| <b>0-40</b>   | 1703   | 29.9  | 32.9     |
| <b>0-60</b>   | 3238   | 56.8  | 62.5     |
| <b>0-90</b>   | 4330   | 76.0  | 83.7     |
| <b>90-180</b> | 846    | 14.8  | 16.3     |
| <b>0-180</b>  | 5176   | 90.8  | 100.0    |

Candela

| Angle      | Along H | 45°  | Across L |
|------------|---------|------|----------|
| <b>0</b>   | 1278    | 1278 | 1278     |
| <b>10</b>  | 1258    | 1264 | 1268     |
| <b>20</b>  | 1195    | 1214 | 1228     |
| <b>30</b>  | 1092    | 1133 | 1180     |
| <b>40</b>  | 952     | 1039 | 1174     |
| <b>50</b>  | 781     | 972  | 1075     |
| <b>60</b>  | 582     | 817  | 724      |
| <b>70</b>  | 367     | 472  | 553      |
| <b>80</b>  | 157     | 251  | 138      |
| <b>90</b>  | 15      | 30   | 21       |
| <b>100</b> | 31      | 65   | 50       |
| <b>110</b> | 96      | 18   | 38       |
| <b>120</b> | 169     | 45   | 20       |
| <b>130</b> | 240     | 140  | 64       |
| <b>140</b> | 304     | 244  | 173      |
| <b>150</b> | 358     | 286  | 286      |
| <b>160</b> | 398     | 369  | 311      |
| <b>170</b> | 424     | 426  | 420      |
| <b>180</b> | 434     | 434  | 434      |

ORDERING INFORMATION

SAMPLE NUMBER: DMF-232-120V-EB81-U

|                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                                                                                                                  |                                                                                                                                                                                                                                                       |                                              |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------|
| <b>Tandem</b><br>Blank=4' Length<br>8T=8' Length<br><br><b>Series</b><br>DMF= Apertured Reflector<br>DCMF= Closed Top Reflector<br><br><b>Lamp Spacing</b><br>Blank=Standard Spacing<br>N=Narrow Spacing for 2 Lamp Only (10% uplight) | <b>Number of Lamps</b><br>2, 3 or 4 Lamps (Not included)<br><br><b>Wattage (Length)</b><br>32=32W T8 (48")<br><br><b>Voltage <sup>(1)</sup></b><br>120V=120 Volt<br>277V=277 Volt<br>347V=347 Volt<br>UNV=Universal Voltage 120-277<br><br><b>Options</b><br>GL=Single Element Fuse<br>GM=Double Element Fuse<br>EL=Emergency Installed | <b>Ballast Type <sup>(1)</sup></b><br>EB8 =T8 Electronic Instant Start.<br>Total Harmonic Distortion < 10%<br>No. of Ballast<br>1, 2 or 3<br>EB8 /PLUS=T8 Electronic Instant Start.<br>High Ballast Factor >1.13.<br>Total Harmonic Distortion < 20%<br>No. of Ballast<br>1, 2 or 3<br>ER8 =T8 Electronic Program Rapid Start.<br>Total Harmonic Distortion < 10%<br>No. of Ballast<br>1, 2 or 3 | <b>Options</b><br>6-3/18 SJT-C&P-515P=Cord & Plug (120V)<br>6-3/18 SJT-C&P-L715P=Cord & Plug (277V)<br>PI/CPI=Plug-In Option<br>TILW=Tandem In-Line Wiring Option (Consult TILW Option Catalog Page)<br>POX=Porlux Finish (See options & accessories) | <b>Packaging</b><br>U=Unit Pack<br>4B=4 Bulk |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------|

ACCESSORIES

(Order Separately)

**A1B/Spacer-U**=Spacer 1-1/2" to 2-1/2" from ceiling (Use 2 per fixture)

**ATG-DIF-4-U**=Tong Hanger (Use 2 per fixture)

**SCF**=Fixed Stem Set (Specify Length)

**SCS**=Swivel Stem Set (Specify Length)

**SCA**=Adjustable 48" Stem Set

**AYC-Chain/Set-U**=Chain Hanger Set (Use 1 set per fixture)

**WG/DIF4FT-U**=Wire Guard

**GYM GUARD, GG-DIF**=Wire Gym Guard

**MECL-DIF/RS-49-3/4-U**=Metal Egg Crate Louver

**MECL-DIF/RS-99-1/2-U**=Metal Egg Crate Louver

**DIF2 LONG CONN (PREPAINTED)**=Long Connector

**DIF CLOSED END PLATE**=Closed End Plate

SHIPPING DATA

| Catalog No. | Wt.     |
|-------------|---------|
| DMF-232     | 15 lbs. |
| 8TDMF-232   | 30 lbs. |
| DMF-332     | 25 lbs. |
| DMF-432     | 25 lbs. |

NOTES: <sup>(1)</sup>Products also available in non-US voltages and frequencies for international markets.

Specifications & dimensions subject to change without notice. Consult your Cooper Lighting Representative for availability and ordering information.