



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DV18250BCY 22-18 Vinyl Ins Female Disconnect Red Panduit Corporation

Catalog Number	DV18250BCY
Manufacturer	Panduit Corporation
Description	The Vibration Resistant Female Disconnect Is Made Of Brass and Is Tin-Plated. It Is Barrel Insulated In Red Vinyl Housing. It Has A Tab Size Of 0.250 X 0.032" (6.3 X 0.8 MM) and Supports A Wire Range Of 22-18 Awg (0.5-1.0 MM ²). It Is 0.81" (20.6 MM) Long and 0.29" (7.4 MM) Wide. The Disconnect Has A Funnel Entry Barrel Configuration and A Butted Seam Barrel. It Comes In Bottles Of 100.
Weight per unit	0.2300 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel Entry
Voltage Rating	600

Descriptions

Description	22-18 VINYL INS FEMALE DISCONNECT RED
extra long description	PAN DV18-250B-CY Pan-Term® DV18-250
Long Description	The vibration resistant female disconnect is made of brass and is tin-plated. It is barrel insulated in red vinyl housing. It has a tab size of 0.250 x 0.032" (6.3 x 0.8 mm) and supports a wire range of 22-18 AWG (0.5-1.0 mm ²). It is 0.81" (20.6 mm) long and 0.29" (7.4 mm) wide. The disconnect has a funnel entry barrel configuration and a butted seam barrel. It comes in bottles of 100.
Product Type	Pan-Term® DV18-250B-Cy Loose Piece Disconnect

Manufacturer Information

Brand	PANDUIT
GTIN	00074983685615
Manufacturers Part Number	DV18-250B-CY
UPC	074983685615

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
----------------------	-----------

Availability

minimum qty	100
-------------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton.....	100.....
Package.....	500.....
Weight Per each.....	0.23.....

Uses, Certifications, and Standards

Temperature Rating.....	221 Degrees Fahrenheit (105 Degrees Celsius).....
-------------------------	---