



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DNF14250FIL 16-14AWG Blu Insldt FML DSCNCT *Panduit Corporation*

Catalog Number	DNF14250FIL
Manufacturer	Panduit Corporation
Description	The Vibration Resistant Female Disconnect Is Made Of Brass and Is Tin-Plated. It Is Fully Insulated In A Blue, Nylon Housing. It Has A Tab Size Of 0.250 X 0.032" (6.3 X 0.8 MM) and Supports A Wire Range Of 16-14 Awg (1.5-2.5 MM <sup>2</sup> ). It Is 0.94" (23.9 MM) Long and 0.36" (9.1 MM) Wide. The Disconnect Has A Funnel Entry Barrel Configuration and An Insulation Grip Sleeve Barrel. It Comes In Bottles Of 50.
Weight per unit	0.1650 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

connection	Funnel Entry
Voltage Rating	600

### Descriptions

Description	16-14AWG BLU INSLTD FML DSCNCT
extra long description	PAN DNF14-250FI-L Pan-Term® DNF14-2
Long Description	The vibration resistant female disconnect is made of brass and is tin-plated. It is fully insulated in a blue, nylon housing. It has a tab size of 0.250 x 0.032" (6.3 x 0.8 mm) and supports a wire range of 16-14 AWG (1.5-2.5 mm <sup>2</sup> ). It is 0.94" (23.9 mm) long and 0.36" (9.1 mm) wide. The disconnect has a funnel entry barrel configuration and an insulation grip sleeve barrel. It comes in bottles of 50.
Product Type	Pan-Term® DNF14-250FI-L Loose Piece Disconnect

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983119066
Manufacturers Part Number	DNF14-250FI-L
UPC	074983119066

### Packaging

Carton	50
Package	250
Weight Per each	0.165

### Uses, Certifications, and Standards

Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
--------------------	--