



DSD923 2Ckt 2POS Sel-SW

Crouse-Hinds

Catalog Number	DSD923
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series DSD Selector Switch Cover and Device Sub-Assembly, 10A, Feraloy Iron Alloy, 2 Position, 2 Circuit, Factory Sealed, Maintained Contact, 600 Vac
Weight per unit	3.8 (lbs/each)
Product Category	Control Station Cover Assembl

Features

action	Maintained
amperage rating	10
dimensions	5.2000 IN X 6.8000 IN X 4.6000 IN
Material	FERALOY IRON ALLOY
Voltage Rating	600 VAC

Descriptions

Description	2Ckt 2POS SEL-SW
extra long description	CRS-H DSD923 DSD COVER DEVICE SUB-A
Features	New DSDX series available with NEMA 4X protection for Class I, Division 2 hazardous areas. Crouse-Hinds series DSD and DSDX explosionproof cover and device sub-assemblies are for use with our EDS/EDSC back boxes and EDSCM modular multi-gang device bodies. DSD/DSDX covers are available with a wide variety of devices and configurations, including manual motor starters, front operated pushbuttons, general use snap switches, side operated pushbuttons, selector switches and pilot lights. Certified for use in CI
Long Description	Eaton Crouse-Hinds series DSD selector switch cover and device sub-assembly, 10A, Feraloy iron alloy, 2 position, 2 circuit, Factory sealed, Maintained contact, 600 Vac
Product Type	DSD Cover Device Sub-Assembly 2 Cir Univ
Special Features	Factory sealed

Manufacturer Information

Brand	Eaton
GTIN	00782274235325
Manufacturers Part Number	DSD923
UPC	782274235325

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION MOTOR CONTROL
Type	Selector switch cover and device sub-assembly



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street
72758-6430, AR Rogers
Phone: 479-636-4190
Fax: 479-636-5604

Packaging

Carton	1
Weight Per each	3.75

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
Enclosure	Class I Div 1 2 Group B C D, Class II Div 1 Group E F G, Class II Div 2 Group F G, Class III, NEMA 3/7B/7C/7D/9E/9F/9G
standard	UL 1203, CSA C22.2