



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E22LED120RD 120V Ac/DC Red Led

Eaton Corp

Catalog Number	E22LED120RD
Manufacturer	Eaton Corp
Description	Pilot Devices - Ashville Pushbutton, Led Lamp, Red, Red, Red, Continuous, 120 Vac/VDC, 22.5 MM, Led Lamp, E22, 10250T, E34 and E22 Units
Weight per unit	0.0010 (lbs/each)
Product Category	Push Button Components

### Dimensions and Weight

Depth	0.1
Height	0.1
Size	22.5 mm
Width	0.1

### Descriptions

Description	120V AC/DC RED LED
extra long description	ETN E22LED120RN 120V AC/DC RED LED
Features	Eaton's 22.5 mm industrial heavy-duty pushbutton line offers a wide array of functional, smartly styled illuminated and non-illuminated pushbuttons, selector switches, push-pulls, action and twist-to- release operators. The complete line also includes transformer, full voltage, resistor, LED or neon light units.
Long Description	Pilot Devices - Ashville Pushbutton, LED Lamp, Red, Red, Red, Continuous, 120 Vac/Vdc, 22.5 mm, LED lamp, E22, 10250T, E34 and E22 units
Product Type	120V Ac/DC Red Led
Special Features	LED

### Manufacturer Information

Brand	Eaton
GTIN	00782113494050
Manufacturers Part Number	E22LED120RN
UPC	782113494050

### Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
Type	Pushbutton accessory

### Availability

Status	Inactive
--------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.001

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
standard	CSA Std. C22.2, Lloyd's Register Certified, BS 4794, IEC 337-1, UL 508, IEC 947-5-1 MTTA, CE Marked