



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DV14250MBC 16-14 Vinyl Ins Male Disconnect Blue *Panduit Corporation*

| | |
|------------------|--|
| Catalog Number | DV14250MBC |
| Manufacturer | Panduit Corporation |
| Description | The Vibration Resistant Male Disconnect Is Made Of Copper and Is Nickel-Plated. It Is Barrel Insulated In Blue Vinyl Housing. It Has A Tab Size Of 0.250 X 0.032" (6.3 X 0.8 MM) and Supports A Wire Range Of 16-14 Awg (1.5-2.5 MM ²). It Is 0.96" (24.4 MM) Long and 0.25" (6.4 MM) Wide. The Disconnect Has A Funnel Entry Barrel Configuration and A Butted Seam Barrel. It Comes In Bottles Of 100. |
| Weight per unit | 1.0 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|--------------|
| connection | Funnel Entry |
| insulation | Vinyl |
| Material | Copper |
| Voltage Rating | 600 |
| Wire Size | 14 |

Material, Color, and Finish

| | |
|--------|---------------|
| Color | Blue |
| Finish | Nickel Plated |

Descriptions

| | |
|------------------------|--|
| Description | 16-14 VINYL INS MALE DISCONNECT BLUE |
| extra long description | PAN DV14-250MB-C Pan-Term® DV14-250 |
| Long Description | The vibration resistant male disconnect is made of copper and is nickel-plated. It is barrel insulated in blue vinyl housing. It has a tab size of 0.250 x 0.032" (6.3 x 0.8 mm) and supports a wire range of 16-14 AWG (1.5-2.5 mm ²). It is 0.96" (24.4 mm) long and 0.25" (6.4 mm) wide. The disconnect has a funnel entry barrel configuration and a butted seam barrel. It comes in bottles of 100. |
| Product Type | Pan-Term® DV14-250MB-C Loose Piece Disconnect |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983822256 |
| Manufacturers Part Number | DV14-250MB-C |
| UPC | 074983822256 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------|
| Category Description | TERMINALS |
| Type | Disconnect |

Availability

| | |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

Packaging

| | |
|-----------------|-----|
| Carton | 100 |
| Package | 500 |
| Weight Per each | 1 |

Uses, Certifications, and Standards

| | |
|--------------------|---|
| Mounting | 1932-09-01 |
| standard | CSA Certified LR31212, C22.2 No.153;UL 310 Listed, UL Listed 20H3 E78522 |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius) |