



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E5218RU04B1 Rect Ind Prox 3W DC PNP *Eaton Corp*

Catalog Number	E5218RU04B1
Manufacturer	Eaton Corp
Description	Eaton E52 Inductive Proximity Sensor, Inductive Proximity Sensor, E52, Unshielded, Led Indicator, 6.6 FT, 100 Ma, PVC, NC PNP Open Collector, 10-30 VDC
Weight per unit	0.5000 (lbs/each)
Product Category	Inductive Proximity Sensor

Features

dimensions	1.1800 IN X 0.7100 IN X 0.3900 IN
------------	-----------------------------------

Descriptions

Description	RECT IND PROX 3W DC PNP
extra long description	ETN E52-18RU04-B1 RECT IND PROX 3W
Features	Built sensor tough E52 rectangular style – Eaton's E52 rectangular-style inductive proximity sensors feature a compact, space-saving design for applications where tubular sensors cannot be used. These 3-wire DC devices are constructed with robust PBT housings for corrosion resistance, and they are epoxy filled to withstand shock and vibration. Bright indicator LEDs are available on all models to clearly show sensor status. E52 cube style – Eaton's E52 cube-style sensors deliver rugged, robust, long-range
Long Description	Eaton E52 inductive proximity sensor, Inductive Proximity Sensor, E52, Unshielded, LED indicator, 6.6 ft, 100 mA, PVC, NC PNP open collector, 10-30 Vdc
Product Type	Rect Ind Prox 3W DC PNP

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114013229
Manufacturers Part Number	E52-18RU04-B1
UPC	782114013229

Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Inductive Proximity Sensor

Packaging

Carton	1
Weight Per each	0.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Stationary Mach Equip In Factory - Other Stationary Machinery
and Equipment - In Factory

environmental conditions

NEMA 1, NEMA 2, NEMA 3, NEMA 3S, NEMA 4, NEMA 12, IP66

standard

UL Listed