



## DV14250MBC 16-14 Vinyl Ins Male Disconnect Blue

*Panduit Corporation*

Catalog Number

DV14250MBC

Manufacturer

Panduit Corporation

Description

The Vibration Resistant Male Disconnect Is Made Of Copper and Is Nickel-Plated. It Is Barrel Insulated In Blue Vinyl Housing. It Has A Tab Size Of 0.250 X 0.032" (6.3 X 0.8 MM) and Supports A Wire Range Of 16-14 Awg (1.5-2.5 MM<sup>2</sup>). It Is 0.96" (24.4 MM) Long and 0.25" (6.4 MM) Wide. The Disconnect Has A Funnel Entry Barrel Configuration and A Butted Seam Barrel. It Comes In Bottles Of 100.

Weight per unit

1.0 (lbs/each)

Product Category

Small Terminals & Connectors

### Features

connection

Funnel Entry

insulation

Vinyl

Material

Copper

Voltage Rating

600

Wire Size

14

### Material, Color, and Finish

Color

Blue

Finish

Nickel Plated

### Descriptions

Description

16-14 VINYL INS MALE DISCONNECT BLUE

extra long description

PAN DV14-250MB-C Pan-Term® DV14-250

Long Description

The vibration resistant male disconnect is made of copper and is nickel-plated. It is barrel insulated in blue vinyl housing. It has a tab size of 0.250 x 0.032" (6.3 x 0.8 mm) and supports a wire range of 16-14 AWG (1.5-2.5 mm<sup>2</sup>). It is 0.96" (24.4 mm) long and 0.25" (6.4 mm) wide. The disconnect has a funnel entry barrel configuration and a butted seam barrel. It comes in bottles of 100.

Product Type

Pan-Term® DV14-250MB-C Loose Piece Disconnect



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2001 ATKINSON DRIVE  
75901-0000, TX Lufkin  
Phone: 936-632-9733  
Fax: 936-632-9736

## Manufacturer Information

Brand	PANDUIT
GTIN	00074983822256
Manufacturers Part Number	DV14-250MB-C
UPC	074983822256

## Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Disconnect

## Availability

minimum qty	100
-------------	-----

## Packaging

Carton	100
Package	500
Weight Per each	1

## Uses, Certifications, and Standards

Mounting standard	9/32
	CSA Certified LR31212, C22.2 No.153;UL 310 Listed, UL Listed 20H3 E78522
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)