



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2414 Montgomery Ln.  
71111-0000, LA Bossier City  
Phone: 318-746-5712  
Fax: 318-746-8036



## DVCL153PWH Diva 150W Led 3WAY White Lutron

Catalog Number	DVCL153PWH
Manufacturer	Lutron
Description	Dimmable Bulb, Wallbox Switch, 120 V, 150 W;6000 W, 60 HZ, Dimmable CFL/Led;Incandescent/Halogen Lamp, Wall Mount, 2.94 In Length, 2.75 In Width, 4.69 In Height, White, +32 °F Operating Temperature, +104 °F Operating Temperature, 1 Yr Warranty, 0.25 LB/Ea
Weight per unit	0.2500 (lbs/each)
Product Category	Lighting Dimmers

### Features

actuator	Paddle Switch
connection	Wire Leads
Connection Type	Wire Leads
insulation	Plastic
Material	Plastic/Metal
media	Yes
Poles	1
Voltage Rating	120
Wattage	600

### Material, Color, and Finish

Finish	Gloss
--------	-------

### Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------

### Descriptions

Description	DIVA 150W LED 3WAY WHITE
extra long description	LUT DVCL-153P-WH DIVA CFL/LED BOXED
Special Features	Controls 150 W dimmable LED/CFL (screw-base), 600 W incandescent, or halogen loads. Paddle turns on/off. Slide up to brighten, down to dim. Provides reliable dimming of dimmable LEDs/CFLs, as well as halogens and incandescents.

### Manufacturer Information

GTIN	00027557003056
UPC	027557003056

### Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer, 3-way/single-pole



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2414 Montgomery Ln.  
71111-0000, LA Bossier City  
Phone: 318-746-5712  
Fax: 318-746-8036

## Packaging

Carton	1
Weight Per each	0.25

## Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	Indoor use only
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, CSA, NOM