

# Eaton ECN5532CAG

Catalog Number: ECN5532CAG

Eaton Freedom Industrial Pump Panel, Circuit breaker disconnect, NEMA 3R painted steel enclosure, 440V/50 Hz-460V/60 Hz coil, NEMA size 3, 100A breaker



## General specifications

|                             |                             |
|-----------------------------|-----------------------------|
| <b>Product Name</b>         | <b>Catalog Number</b>       |
| Eaton Industrial pump panel | ECN5532CAG                  |
| <b>UPC</b>                  | <b>Product Length/Depth</b> |
| 782114139134                | 8.47 in                     |
| <b>Product Height</b>       | <b>Product Width</b>        |
| 38.4 in                     | 18.86 in                    |
| <b>Product Weight</b>       | <b>Warranty</b>             |
| 75 lb                       | 1 year                      |

## Certifications

cUL Listed  
OSHDP Certified  
UL Listed

## Product specifications

### Coil voltage

440V/50 Hz-460V/60 Hz

### Enclosure

NEMA 3R

### Enclosure material

Painted steel

### Type

Circuit breaker disconnect

### Circuit breaker rating

100A

### Size

NEMA size 3

## Resources

### Catalogs

[Eaton's Volume 10—Enclosed Control](#)

### Specifications and datasheets

[Eaton Specification Sheet - ECN5532CAG](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton ECN5532CAG

Catalog Number: ECN5532CAG

Eaton Freedom Industrial Pump Panel, Circuit breaker disconnect, NEMA 3R painted steel enclosure, 440V/50 Hz-460V/60 Hz coil, NEMA size 3, 100A breaker



## General specifications

|                             |                             |
|-----------------------------|-----------------------------|
| <b>Product Name</b>         | <b>Catalog Number</b>       |
| Eaton Industrial pump panel | ECN5532CAG                  |
| <b>UPC</b>                  | <b>Product Length/Depth</b> |
| 782114139134                | 8.47 in                     |
| <b>Product Height</b>       | <b>Product Width</b>        |
| 38.4 in                     | 18.86 in                    |
| <b>Product Weight</b>       | <b>Warranty</b>             |
| 75 lb                       | 1 year                      |

## Certifications

cUL Listed  
OSHDP Certified  
UL Listed

## Product specifications

### Coil voltage

440V/50 Hz-460V/60 Hz

### Enclosure

NEMA 3R

### Enclosure material

Painted steel

### Type

Circuit breaker disconnect

### Circuit breaker rating

100A

### Size

NEMA size 3

## Resources

### Catalogs

[Eaton's Volume 10—Enclosed Control](#)

### Specifications and datasheets

[Eaton Specification Sheet - ECN5532CAG](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)