




GE
Lighting

97590 - F13DBX/827/ECO

GE Ecolux® Biax® T4 - Facilities; Retail Display; Hospitality; Office; Restaurant; Warehouse




CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
 - Remove and install by grasping only plastic portion of the lamp.

GRAPHS & CHARTS

Graphs_Spectral Power Distribution



NOTES

- Based on 60Hz reference circuit.
- Fluorescent lamp lumens decline during life

GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Plug-In
Bulb	T4
Base	G24d-1
Equivalent Wattage (NOM)	60.0 W
Rated Life (NOM)	10000.0 h
Starting Temperature (MIN)	-15.0 °C
Cathode Resistance (NOM)	10.5 Ohm
Mercury Content (NOM)	3.0 mg
Picograms of Mercury (NOM)	397.351 pg
Additional Info	TCLP compliant
Primary Application	Facilities;Retail Display;Hospitality;Office;Restaurant;Warehouse

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	900.0
Mean Lumens (NOM)	755.0
Nominal Initial Lumens per Watt (NOM)	69.23077
Color Temperature (NOM)	2700.0 K
Color Rendering Index (CRI) (NOM)	82.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	13.0
Voltage (NOM)	91.0
Open Circuit Voltage Across Starter (MIN)	198.0 V
Lamp Current (NOM)	0.175 A
Current Crest Factor (MAX)	1.7
Supply Current Frequency (NOM)	60.0 Hz

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	5.240 in(133.1 mm)
Nominal Length (NOM)	5.300 in(134.6 mm)
Base Face to Top of Lamp (NOM)	4.370 in(111.0 mm)

PRODUCT INFORMATION


Product Code	97590
Description	F13DBX/827/ECO
ANSI Code	60901-IEC-0513-1
Standard Package	BUNDLE
Standard Package GTIN	
Standard Package Quantity	50
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	50
UPC	043168975902



GE
Lighting

97590 - F13DBX/827/ECO

GE Ecolux® Biax® T4 - Facilities; Retail Display; Hospitality; Office; Restaurant; Warehouse




CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
 - Remove and install by grasping only plastic portion of the lamp.

GRAPHS & CHARTS

Graphs_Spectral Power Distribution



NOTES

- Based on 60Hz reference circuit.
- Fluorescent lamp lumens decline during life

GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Plug-In
Bulb	T4
Base	G24d-1
Equivalent Wattage (NOM)	60.0 W
Rated Life (NOM)	10000.0 h
Starting Temperature (MIN)	-15.0 °C
Cathode Resistance (NOM)	10.5 Ohm
Mercury Content (NOM)	3.0 mg
Picograms of Mercury (NOM)	397.351 pg
Additional Info	TCLP compliant
Primary Application	Facilities;Retail Display;Hospitality;Office;Restaurant;Warehouse

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	900.0
Mean Lumens (NOM)	755.0
Nominal Initial Lumens per Watt (NOM)	69.23077
Color Temperature (NOM)	2700.0 K
Color Rendering Index (CRI) (NOM)	82.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	13.0
Voltage (NOM)	91.0
Open Circuit Voltage Across Starter (MIN)	198.0 V
Lamp Current (NOM)	0.175 A
Current Crest Factor (MAX)	1.7
Supply Current Frequency (NOM)	60.0 Hz

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	5.240 in(133.1 mm)
Nominal Length (NOM)	5.300 in(134.6 mm)
Base Face to Top of Lamp (NOM)	4.370 in(111.0 mm)

PRODUCT INFORMATION

Product Code	97590
Description	F13DBX/827/ECO
ANSI Code	60901-IEC-0513-1
Standard Package	BUNDLE
Standard Package GTIN	
Standard Package Quantity	50
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	50
UPC	043168975902