

EI200 Series

Electronic In-Wall Timers

The EI200 Series Decorator Electronic Auto Shut-Off Timers provide silent operation in time ranges from 5 minutes to 12 hours.

Features

- Silent operation in time ranges from 30 minutes to 12 hours
- Replaces single-pole switches in a variety of applications
- Requires neutral wire
- Available with and without HOLD feature
- Single button time selection
- Operates all load types including CFLs, LED lamps, and fans
- Models without HOLD feature meet Title 24 requirements

Not for use with sunlamps, saunas, or loads that could cause personal injury if timed incorrectly.

Ratings

Switch Type: Single Pole

Switch Ratings:

Resistive (heater): 15 Amp, 120 VAC, 1800 Watts

Tungsten (incandescent): 8.3 Amp, 120 VAC, 1000 Watts

Ballast (magnetic): 8 Amp, 120 VAC

Electronic Ballast: 500VA

Motor: ¼ HP, 120 VAC

Input Voltage: 120 VAC, 60 Hz

Operating Temperature: 32°F to 122°F (0°C to 50°C)

Style: For use with decorator switch plates

Dimenisions: 2.79" H x 1.75" W x 1.44" D

Warranty: Limited 1 year

Project: _____

Location: _____

Product Type: _____

Contact/Phone: _____

Model #: _____




| Model Number | Time Range | Switch | Clock Volts AC | Max Wattage | Neutral Required | Color | Hold |
|--------------|---------------------------|-------------|----------------|-------------|------------------|--------------|------|
| EI200 | 5/10/15/30 Minute | Single-Pole | 120 | 1800 | Yes | Ivory | Yes |
| EI200W | 5/10/15/30 Minute | Single-Pole | 120 | 1800 | Yes | White | Yes |
| EI200LA | 5/10/15/30 Minute | Single-Pole | 120 | 1800 | Yes | Light Almond | Yes |
| EI205 | 5/15/30/45/60 Minute | Single-Pole | 120 | 1800 | Yes | Ivory | No |
| EI205W | 5/15/30/45/60 Minute | Single-Pole | 120 | 1800 | Yes | White | No |
| EI205LA | 5/15/30/45/60 Minute | Single-Pole | 120 | 1800 | Yes | Light Almond | No |
| EI210 | 10/20/30/60 Minute | Single-Pole | 120 | 1800 | Yes | Ivory | Yes |
| EI210W | 10/20/30/60 Minute | Single-Pole | 120 | 1800 | Yes | White | Yes |
| EI210LA | 10/20/30/60 Minute | Single-Pole | 120 | 1800 | Yes | Light Almond | Yes |
| EI215 | 15/30/60 Minute, 2/4 Hour | Single-Pole | 120 | 1800 | Yes | Ivory | No |
| EI215W | 15/30/60 Minute, 2/4 Hour | Single-Pole | 120 | 1800 | Yes | White | No |
| EI215LA | 15/30/60 Minute, 2/4 Hour | Single-Pole | 120 | 1800 | Yes | Light Almond | No |
| EI220 | 1/2/4/8 Hour | Single-Pole | 120 | 1800 | Yes | Ivory | Yes |
| EI220W | 1/2/4/8 Hour | Single-Pole | 120 | 1800 | Yes | White | Yes |
| EI220LA | 1/2/4/8 Hour | Single-Pole | 120 | 1800 | Yes | Light Almond | Yes |
| EI230 | 2/4/8/12 Hour | Single-Pole | 120 | 1800 | Yes | Ivory | Yes |
| EI230W | 2/4/8/12 Hour | Single-Pole | 120 | 1800 | Yes | White | Yes |
| EI230LA | 2/4/8/12 Hour | Single-Pole | 120 | 1800 | Yes | Light Almond | Yes |
| EI235 | 15/30/45/60/120 Minute | Single-Pole | 120 | 1800 | Yes | Ivory | No |
| EI235W | 15/30/45/60/120 Minute | Single-Pole | 120 | 1800 | Yes | White | No |
| EI235LA | 15/30/45/60/120 Minute | Single-Pole | 120 | 1800 | Yes | Light Almond | No |

Specification

The timer shall be supplied with an LED and single-button operation. The timer must fit a standard wall box and accept a rectangular decorator wall plate. Timer contacts shall break current at the end of timed cycle. The timer shall be capable of single-pole operation. Various user selectable timing ranges shall be available up to 12 hours, with or without "HOLD" feature for constant ON. The timer shall be Intermatic model _____ (See Model Numbers Listed).

Diagrams



EI200 Series

Electronic In-Wall Timers

The EI200 Series Decorator Electronic Auto Shut-Off Timers provide silent operation in time ranges from 5 minutes to 12 hours.

Features

- Silent operation in time ranges from 30 minutes to 12 hours
- Replaces single-pole switches in a variety of applications
- Requires neutral wire
- Available with and without HOLD feature
- Single button time selection
- Operates all load types including CFLs, LED lamps, and fans
- Models without HOLD feature meet Title 24 requirements

Not for use with sunlamps, saunas, or loads that could cause personal injury if timed incorrectly.

Ratings

| | |
|--------------------------|--------------------------------------|
| Switch Type: | Single Pole |
| Switch Ratings: | |
| Resistive (heater): | 15 Amp, 120 VAC, 1800 Watts |
| Tungsten (incandescent): | 8.3 Amp, 120 VAC, 1000 Watts |
| Ballast (magnetic): | 8 Amp, 120 VAC |
| Electronic Ballast: | 500VA |
| Motor: | ¼ HP, 120 VAC |
| Input Voltage: | 120 VAC, 60 Hz |
| Operating Temperature: | 32°F to 122°F (0°C to 50°C) |
| Style: | For use with decorator switch plates |
| Dimenisions: | 2.79" H x 1.75" W x 1.44" D |
| Warranty: | Limited 1 year |

Project: _____

Location: _____

Product Type: _____

Contact/Phone: _____

Model #: _____



| Model Number | Time Range | Switch | Clock Volts AC | Max Wattage | Neutral Required | Color | Hold |
|--------------|---------------------------|-------------|----------------|-------------|------------------|--------------|------|
| EI200 | 5/10/15/30 Minute | Single-Pole | 120 | 1800 | Yes | Ivory | Yes |
| EI200W | 5/10/15/30 Minute | Single-Pole | 120 | 1800 | Yes | White | Yes |
| EI200LA | 5/10/15/30 Minute | Single-Pole | 120 | 1800 | Yes | Light Almond | Yes |
| EI205 | 5/15/30/45/60 Minute | Single-Pole | 120 | 1800 | Yes | Ivory | No |
| EI205W | 5/15/30/45/60 Minute | Single-Pole | 120 | 1800 | Yes | White | No |
| EI205LA | 5/15/30/45/60 Minute | Single-Pole | 120 | 1800 | Yes | Light Almond | No |
| EI210 | 10/20/30/60 Minute | Single-Pole | 120 | 1800 | Yes | Ivory | Yes |
| EI210W | 10/20/30/60 Minute | Single-Pole | 120 | 1800 | Yes | White | Yes |
| EI210LA | 10/20/30/60 Minute | Single-Pole | 120 | 1800 | Yes | Light Almond | Yes |
| EI215 | 15/30/60 Minute, 2/4 Hour | Single-Pole | 120 | 1800 | Yes | Ivory | No |
| EI215W | 15/30/60 Minute, 2/4 Hour | Single-Pole | 120 | 1800 | Yes | White | No |
| EI215LA | 15/30/60 Minute, 2/4 Hour | Single-Pole | 120 | 1800 | Yes | Light Almond | No |
| EI220 | 1/2/4/8 Hour | Single-Pole | 120 | 1800 | Yes | Ivory | Yes |
| EI220W | 1/2/4/8 Hour | Single-Pole | 120 | 1800 | Yes | White | Yes |
| EI220LA | 1/2/4/8 Hour | Single-Pole | 120 | 1800 | Yes | Light Almond | Yes |
| EI230 | 2/4/8/12 Hour | Single-Pole | 120 | 1800 | Yes | Ivory | Yes |
| EI230W | 2/4/8/12 Hour | Single-Pole | 120 | 1800 | Yes | White | Yes |
| EI230LA | 2/4/8/12 Hour | Single-Pole | 120 | 1800 | Yes | Light Almond | Yes |
| EI235 | 15/30/45/60/120 Minute | Single-Pole | 120 | 1800 | Yes | Ivory | No |
| EI235W | 15/30/45/60/120 Minute | Single-Pole | 120 | 1800 | Yes | White | No |
| EI235LA | 15/30/45/60/120 Minute | Single-Pole | 120 | 1800 | Yes | Light Almond | No |

Specification

The timer shall be supplied with an LED and single-button operation. The timer must fit a standard wall box and accept a rectangular decorator wall plate. Timer contacts shall break current at the end of timed cycle. The timer shall be capable of single-pole operation. Various user selectable timing ranges shall be available up to 12 hours, with or without "HOLD" feature for constant ON. The timer shall be Intermatic model _____ (See Model Numbers Listed).

Diagrams

