



GE
Lighting


45742 - F17T8/SPX30/ECO

GE Ecolux® Starcoat® T8

- Passes TCLP, which can lower disposal costs.



High Color Rendering



CAUTIONS & WARNINGS

Caution


- Lamp may shatter and cause injury if broken
 - Wear safety glasses and gloves when handling lamp.
 - Do not use excessive force when installing lamp.

Warning


- Risk of Electric Shock
 - Turn power off before inspection, installation or removal.

GRAPHS & CHARTS

Graphs_Spectral Power Distribution



Graphs_Lumen Maintenance



Graphs_Lamp Mortality

For additional information, visit www.gelighting.com

GENERAL CHARACTERISTICS

| | |
|-----------------------------------|--------------------------------------|
| Lamp Type | Linear Fluorescent - Straight Linear |
| Bulb | T8 |
| Base | Medium Bi-Pin (G13) |
| Rated Life | 30000.0 hrs |
| Rated Life (instant start) @ Time | 15000 h @ 3 h |
| Rated Life (rapid start) @ Time | 20000 h @ 12 h |
| Bulb Material | Soda lime |
| Starting Temperature (MIN) | 10.0 °C |
| LEED-EB MR Credit | 77 picograms Hg per mean lumen hour |
| Additional Info | TCLP compliant |
| Primary Application | Full Wattage |

PHOTOMETRIC CHARACTERISTICS

| | |
|-------------------------------------|----------|
| Initial Lumens | 1350.0 |
| Mean Lumens | 1280.0 |
| Nominal Initial Lumens per Watt | 79 |
| Color Temperature | 3000.0 K |
| Color Rendering Index (CRI) | 85.0 |
| S/P Ratio (Scotopic/Photopic Ratio) | 1.3 |

ELECTRICAL CHARACTERISTICS


| | |
|--|---------------|
| Wattage | 17.0 |
| Voltage | 70.0 |
| Open Circuit Voltage (rapid start) (MAX) | 285.0 V |
| Open Circuit Voltage (rapid start) Min @ Temperature | 210 V @ 10 °C |
| Cathode Resistance Ratio - Rh/Rc (MIN) | 4.25 |
| Cathode Resistance Ratio - Rh/Rc (MAX) | 6.5 |
| Current Crest Factor (MAX) | 1.7 |

DIMENSIONS

| | |
|--|----------------------|
| Maximum Overall Length (MOL) | 24.0000 in(609.6 mm) |
| Minimum Overall Length | 23.6700 in(601.2 mm) |
| Nominal Length | 24.000 in(609.6 mm) |
| Bulb Diameter (DIA) (MIN) | 0.940 in(23.9 mm) |
| Bulb Diameter (DIA) (MAX) | 1.100 in(27.9 mm) |
| Bulb Diameter (DIA) | 1.000 in(25.4 mm) |
| Max Base Face to Base Face (A) | 23.220 in(589.8 mm) |
| Face to End of Opposing Pin (B) (MIN) | 23.400 in(594.4 mm) |
| Face to End of Opposing Pin (B) (MAX) | 23.500 in(596.9 mm) |
| End of Base Pin to End of Opposite Pin End (C) | 23.670 in(601.2 mm) |

PRODUCT INFORMATION

| | |
|----------------------------------|-----------------|
| Product Code | 45742 |
| Description | F17T8/SPX30/ECO |
| ANSI Code | 1001-1 |
| Standard Package | Case |
| Standard Package GTIN | 10043168457429 |
| Standard Package Quantity | 24 |
| Sales Unit | Unit |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 24 |
| UPC | 043168457422 |





GE
Lighting

45742 - F17T8/SPX30/ECO

GE Ecolux® Starcoat® T8

- Passes TCLP, which can lower disposal costs.



High Color Rendering



GENERAL CHARACTERISTICS

| | |
|-----------------------------------|--------------------------------------|
| Lamp Type | Linear Fluorescent - Straight Linear |
| Bulb | T8 |
| Base | Medium Bi-Pin (G13) |
| Rated Life | 30000.0 hrs |
| Rated Life (instant start) @ Time | 15000 h @ 3 h |
| Rated Life (rapid start) @ Time | 20000 h @ 12 h |
| Bulb Material | Soda lime |
| Starting Temperature (MIN) | 10.0 °C |
| LEED-EB MR Credit | 77 picograms Hg per mean lumen hour |
| Additional Info | TCLP compliant |
| Primary Application | Full Wattage |

PHOTOMETRIC CHARACTERISTICS

| | |
|-------------------------------------|----------|
| Initial Lumens | 1350.0 |
| Mean Lumens | 1280.0 |
| Nominal Initial Lumens per Watt | 79 |
| Color Temperature | 3000.0 K |
| Color Rendering Index (CRI) | 85.0 |
| S/P Ratio (Scotopic/Photopic Ratio) | 1.3 |

ELECTRICAL CHARACTERISTICS


| | |
|--|---------------|
| Wattage | 17.0 |
| Voltage | 70.0 |
| Open Circuit Voltage (rapid start) (MAX) | 285.0 V |
| Open Circuit Voltage (rapid start) Min @ Temperature | 210 V @ 10 °C |
| Cathode Resistance Ratio - Rh/Rc (MIN) | 4.25 |
| Cathode Resistance Ratio - Rh/Rc (MAX) | 6.5 |
| Current Crest Factor (MAX) | 1.7 |

DIMENSIONS

| | |
|--|----------------------|
| Maximum Overall Length (MOL) | 24.0000 in(609.6 mm) |
| Minimum Overall Length | 23.6700 in(601.2 mm) |
| Nominal Length | 24.000 in(609.6 mm) |
| Bulb Diameter (DIA) (MIN) | 0.940 in(23.9 mm) |
| Bulb Diameter (DIA) (MAX) | 1.100 in(27.9 mm) |
| Bulb Diameter (DIA) | 1.000 in(25.4 mm) |
| Max Base Face to Base Face (A) | 23.220 in(589.8 mm) |
| Face to End of Opposing Pin (B) (MIN) | 23.400 in(594.4 mm) |
| Face to End of Opposing Pin (B) (MAX) | 23.500 in(596.9 mm) |
| End of Base Pin to End of Opposite Pin End (C) | 23.670 in(601.2 mm) |

PRODUCT INFORMATION

| | |
|----------------------------------|-----------------|
| Product Code | 45742 |
| Description | F17T8/SPX30/ECO |
| ANSI Code | 1001-1 |
| Standard Package | Case |
| Standard Package GTIN | 10043168457429 |
| Standard Package Quantity | 24 |
| Sales Unit | Unit |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 24 |
| UPC | 043168457422 |



CAUTIONS & WARNINGS

Caution


- Lamp may shatter and cause injury if broken
 - Wear safety glasses and gloves when handling lamp.
 - Do not use excessive force when installing lamp.

Warning


- Risk of Electric Shock
 - Turn power off before inspection, installation or removal.

GRAPHS & CHARTS

Graphs_Spectral Power Distribution



Graphs_Lumen Maintenance



Graphs_Lamp Mortality

For additional information, visit www.gelighting.com

