



GE  
Lighting


## 26667 - F32T8/SP35/ECO

GE Ecolux® Starcoat® T8

- Passes TCLP, which can lower disposal costs.



High Color Rendering  
Meets Federal Minimum Efficiency Standards



### CAUTIONS & WARNINGS

#### Caution


- Lamp may shatter and cause injury if broken
  - Wear safety glasses and gloves when handling lamp.
  - Do not use excessive force when installing lamp.

#### Warning


- Risk of Electric Shock
  - Turn power off before inspection, installation or removal.

### GRAPHS & CHARTS

#### Graphs\_Spectral Power Distribution



#### Graphs\_Lumen Maintenance



### GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life	30000.0 hrs
Rated Life (instant start) @ Time	21000 h @ 3 h
Rated Life (rapid start) @ Time	30000 h @ 12 h
Rated Life (rapid start) @ Time	30000.0 @ 3.0/36000.0 @ 12.0 h
Bulb Material	Soda lime
Starting Temperature (MIN)	10.0 °C
LEED-EB MR Credit	36 picograms Hg per mean lumen hour
Additional Info	TCLP compliant
Primary Application	Full Wattage

### PHOTOMETRIC CHARACTERISTICS

Initial Lumens	2450.0
Mean Lumens	2300.0
Nominal Initial Lumens per Watt	77
Color Temperature	3500.0 K
Color Rendering Index (CRI)	78.0
S/P Ratio (Scotopic/Photopic Ratio)	1.4

### ELECTRICAL CHARACTERISTICS

Wattage	32.0
Voltage	137.0
Open Circuit Voltage (rapid start) Min @ Temperature	315 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.25
Cathode Resistance Ratio - Rh/Rc (MAX)	6.5
Current Crest Factor (MAX)	1.7

### DIMENSIONS

Maximum Overall Length (MOL)	47.7800 in(1213.6 mm)
Minimum Overall Length	47.6700 in(1210.8 mm)
Nominal Length	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (MIN)	0.940 in(23.9 mm)
Bulb Diameter (DIA) (MAX)	1.100 in(27.9 mm)
Bulb Diameter (DIA)	1.000 in(25.4 mm)
Max Base Face to Base Face (A)	47.220 in(1199.4 mm)
Face to End of Opposing Pin (B) (MIN)	47.400 in(1204.0 mm)
Face to End of Opposing Pin (B) (MAX)	47.500 in(1206.5 mm)
End of Base Pin to End of Opposite Pin End (C)	47.670 in(1210.8 mm)

### PRODUCT INFORMATION

Product Code	26667
Description	F32T8/SP35/ECO
ANSI Code	1005-2
Standard Package	Case
Standard Package GTIN	10043168266670
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
UPC	043168266673

Graphs\_Lamp Mortality





GE  
Lighting


## 26667 - F32T8/SP35/ECO

GE Ecolux® Starcoat® T8

- Passes TCLP, which can lower disposal costs.



High Color Rendering  
Meets Federal Minimum Efficiency Standards



### CAUTIONS & WARNINGS

#### Caution


- Lamp may shatter and cause injury if broken
  - Wear safety glasses and gloves when handling lamp.
  - Do not use excessive force when installing lamp.

#### Warning


- Risk of Electric Shock
  - Turn power off before inspection, installation or removal.

### GRAPHS & CHARTS

#### Graphs\_Spectral Power Distribution



#### Graphs\_Lumen Maintenance



### GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life	30000.0 hrs
Rated Life (instant start) @ Time	21000 h @ 3 h
Rated Life (rapid start) @ Time	30000 h @ 12 h
Rated Life (rapid start) @ Time	30000.0 @ 3.0/36000.0 @ 12.0 h
Bulb Material	Soda lime
Starting Temperature (MIN)	10.0 °C
LEED-EB MR Credit	36 picograms Hg per mean lumen hour
Additional Info	TCLP compliant
Primary Application	Full Wattage

### PHOTOMETRIC CHARACTERISTICS

Initial Lumens	2450.0
Mean Lumens	2300.0
Nominal Initial Lumens per Watt	77
Color Temperature	3500.0 K
Color Rendering Index (CRI)	78.0
S/P Ratio (Scotopic/Photopic Ratio)	1.4

### ELECTRICAL CHARACTERISTICS

Wattage	32.0
Voltage	137.0
Open Circuit Voltage (rapid start) Min @ Temperature	315 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.25
Cathode Resistance Ratio - Rh/Rc (MAX)	6.5
Current Crest Factor (MAX)	1.7

### DIMENSIONS

Maximum Overall Length (MOL)	47.7800 in(1213.6 mm)
Minimum Overall Length	47.6700 in(1210.8 mm)
Nominal Length	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (MIN)	0.940 in(23.9 mm)
Bulb Diameter (DIA) (MAX)	1.100 in(27.9 mm)
Bulb Diameter (DIA)	1.000 in(25.4 mm)
Max Base Face to Base Face (A)	47.220 in(1199.4 mm)
Face to End of Opposing Pin (B) (MIN)	47.400 in(1204.0 mm)
Face to End of Opposing Pin (B) (MAX)	47.500 in(1206.5 mm)
End of Base Pin to End of Opposite Pin End (C)	47.670 in(1210.8 mm)

### PRODUCT INFORMATION

Product Code	26667
Description	F32T8/SP35/ECO
ANSI Code	1005-2
Standard Package	Case
Standard Package GTIN	10043168266670
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
UPC	043168266673

Graphs\_Lamp Mortality

