



GE
Lighting

61362 - GE Ecolux® Starcoat® T5

F54T5/850ECO/PRO

☞ Passes TCLP, which can lower disposal costs.

GENERAL CHARACTERISTICS

| | |
|-------------------------------|---------------------------------|
| Base Description | Miniature Bi-Pin |
| Base Type | Pin/Plug-In |
| Mercury Content | 2.5 mg |
| Rated Life Rapid Start - Hrs | 17000 h @ 3 h 20000 h @ 12 h |
| Starting Temp (MIN) C-degrees | -20 °C |
| Bulb Material | Soda lime |
| Rated Life Hours-nominal | 17000 h |
| Primary Application | Full Wattage |
| Base | G5 |
| Bulb Shape | T5 |

PHOTOMETRIC CHARACTERISTICS

| | |
|---------------------------|---------|
| Mean Lumens nominal | 3900 lm |
| Color Rendering Index-CRI | 85 |

PRODUCT INFORMATION

| | |
|----------------------------------|------------------|
| Product Code | 61362 |
| Description | F54T5/850ECO/PRO |
| Alternative Unit Of Measure | CASE |
| Standard Package Quantity | |
| Ean UPC | 043168613620 |
| Standard Package GTIN | 10043168613627 |
| No Of Items Per Sales Unit | |
| No Of Items Per Standard Package | |
| Sales Unit | Case |
| UCC | 043168613620 |

DIMENSIONS

| | |
|---------------------------------------|----------|
| Diameter | 0.62 in |
| Face to End of Opposing Pin (B) <Max> | 45.52 in |
| Face to End of Opposing Pin (B) <Min> | 45.42 in |
| Nominal Length | 45.2 in |

ELECTRICAL CHARACTERISTICS

| | |
|--|------------------|
| Current Crest Factor (MAX) | 1.7 |
| Open Circuit Voltage (rapid start) Min @ Temperature | 520.00 V @ 10 °C |
| Cathode Resistance Ratio - Rh/Rc (MIN) | 4.250 |
| Cathode Resistance Ratio - Rh/Rc (MAX) | 6.500 |
| Rated power (Watts) | 54 W |



GE
Lighting

61362 - GE Ecolux® Starcoat® T5

F54T5/850ECO/PRO

☞ Passes TCLP, which can lower disposal costs.

GENERAL CHARACTERISTICS

| | |
|-------------------------------|---------------------------------|
| Base Description | Miniature Bi-Pin |
| Base Type | Pin/Plug-In |
| Mercury Content | 2.5 mg |
| Rated Life Rapid Start - Hrs | 17000 h @ 3 h 20000 h @ 12 h |
| Starting Temp (MIN) C-degrees | -20 °C |
| Bulb Material | Soda lime |
| Rated Life Hours-nominal | 17000 h |
| Primary Application | Full Wattage |
| Base | G5 |
| Bulb Shape | T5 |

PHOTOMETRIC CHARACTERISTICS

| | |
|---------------------------|---------|
| Mean Lumens nominal | 3900 lm |
| Color Rendering Index-CRI | 85 |

PRODUCT INFORMATION

| | |
|----------------------------------|------------------|
| Product Code | 61362 |
| Description | F54T5/850ECO/PRO |
| Alternative Unit Of Measure | CASE |
| Standard Package Quantity | |
| Ean UPC | 043168613620 |
| Standard Package GTIN | 10043168613627 |
| No Of Items Per Sales Unit | |
| No Of Items Per Standard Package | |
| Sales Unit | Case |
| UCC | 043168613620 |

DIMENSIONS

| | |
|---------------------------------------|----------|
| Diameter | 0.62 in |
| Face to End of Opposing Pin (B) <Max> | 45.52 in |
| Face to End of Opposing Pin (B) <Min> | 45.42 in |
| Nominal Length | 45.2 in |

ELECTRICAL CHARACTERISTICS

| | |
|--|------------------|
| Current Crest Factor (MAX) | 1.7 |
| Open Circuit Voltage (rapid start) Min @ Temperature | 520.00 V @ 10 °C |
| Cathode Resistance Ratio - Rh/Rc (MIN) | 4.250 |
| Cathode Resistance Ratio - Rh/Rc (MAX) | 6.500 |
| Rated power (Watts) | 54 W |