



## FD175A 3/4 Unilet Type FD-1 Gang

Appleton/Oz Gedney

Catalog Number	FD175A
Manufacturer	Appleton/Oz Gedney
Description	Unilets FD Deep Depth 1-Gang Cast Device Box, Number Of Outlet: 1, Material: Copperfree (4/10 Of 1 PCT Maximum) Aluminum, Size: 3/4 In, Cable Entry: (1) 3/4 In Hub, Cubic Capacity: 25 Cu-In, Knockouts: No, Height: 4.56 In, Width: 2.81 In,
Weight per unit	0.8900 (lbs/each)
Product Category	FS & FD Type Boxes & Covers

### Features

Cable Entry	(1) 3/4 IN Hub
Knockouts	FALSE
Material	Copperfree (4/10 Of 1 PCT Maximum) Aluminum
number of outlet	1

### Dimensions and Weight

Size	3/4
------	-----

### Descriptions

Description	3/4 UNILET TYPE FD-1 GANG
extra long description	APP FD175A 3/4 UNILET TYPE FD-1 GAN
Long Description	UNILETS FD Deep Depth 1-Gang Cast Device Box, Number Of Outlet: 1, Material: Copperfree (4/10 Of 1 PCT Maximum) Aluminum, Size: 3/4 IN, Cable Entry: (1) 3/4 IN Hub, Cubic Capacity: 25 CU-IN, Knockouts: No, Height: 4.56 IN, Width: 2.81 IN,

Product Type	3/4 Unilet Type FD-1 Gang
Special Features	Accommodate wiring devices such as switches and receptacles;Accurately tapped, tapered threads for tight, rigid joints, ground continuity;Both malleable iron and aluminum boxes have ridge top construction for positive cover/gasket/box fit;Corrosion-resistant ideal for indoor and outdoor installations;Internal grounding screws standard;Malleable iron for high tensile strength and ductility provides greater resistance to impact and shock;Permit access to conductors for maintenance;Provide excellent service i



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Appleton
GTIN	00781381455695
Manufacturers Part Number	FD175A
UPC	781381455695

## Taxonomies, Classifications, and Categories

Category Description	FS BOXES AND COVERS
Type	FD Deep Depth 1-Gang Cast Device Box

## Packaging

Carton	1
Package	5
Weight Per each	0.89

## Uses, Certifications, and Standards

Application standard	For Use With Threaded Metal Conduit And IMC UL 514 A, UL File Number E2527, CSA C22.2 No. 18.1, CSA 001472 Certified, NEMA FB-1
----------------------	---------------------------------------------------------------------------------------------------------------------------------------